

V7-9W1AE9-357

([Home](#) : [Products](#) : [Sw itches](#) : [MICRO SWITCH™ Basic Sw itches](#) : [Premium V-Basic Sw itches](#) : [V7](#))



Actual product appearance may vary.

V7 Series Miniature Basic Switch, Single Pole Double Throw Circuitry, 15.1 A at 250 Vac, Special Lever Actuator, 110 gf Maximum Operating Force, Silver Contacts, High Temperature, High Temperature, Quick Connect Termination

[click here to download Hi-Res image](#)

Product Specifications

Sw itch Type	MICRO SWITCH™ Miniature 15,9 mm H x 10,2 mm W x 28,8 mm L [0.63 in H x 0.4 in W x 1.14 in L]
Sealed	No
Ampere Rating	15 A
Circuitry	SPDT
Actuator	Special Lever
Termination	Quick Connect
Operating Temperature	-40 °C to 200 °C [-40 °F to 392 °F]
Voltage	250 Vac
Actuator Length	20,6 mm [0.82 in]
Contact Type	Silver
Operating Force (OF)	110 gf max.
Release Force	6 gf min.
Pretravel (PT)	4,39 mm [0.173 in] max.
Overtravel (OT)	2,39 mm [0.094 in] min.
Differential Travel (DT)	1,02 mm [0.040 in] max.
Operating Position (OP)	21,5 mm ±0,94 mm [0.847 ±0.037 in]
Housing Material	PPS
High Temperature	175 °C [347 °F]
Agency Approvals and Standards	UL, CSA
Mounting Centers	22,2 mm [0.88 in]
Tightening Torque	0,56 N m [5.0 in lb]
Weight	8 g [0.3 oz]
Package Height	15,9 mm [0.63 in]
Package Width	10,3 mm [0.40 in]
Package Length	27,8 mm [1.09 in]
Comment	UL: E12252; CSA: LR41370
Availability	Global
UNSPSC Code	39122209
UNSPSC Commodity	39122209 Snap sw itches
Series Name	V7