Combo pH/conductivity testers – although there are 2 models, they are almost identical – just a different conductivity range, so only 1 entry and photo needed.

Conductivity, pH and TDS in one pocket sized meter

- Dual level display shows pH or EC/TDS with C
- Waterproof immersion proof casing also floats!
- Replaceable pH electrode cartridge
- Automatic calibration & temperature compensation

These pocket meters are fully automatic and combine several parameters within one compact and waterproof case. Temperature compensation and calibration is automatic and the meters also incorporate a reading stability indicator to ensure false readings are not taken. Measure either pH, conductivity or Total Dissolved Solids together with temperature in either C or F. All readings are clearly shown on the dual level LCD display.

Specification	HI98129	HI98130
Range	EC 0 to 3999uS/cm TDS 0 to 2000ppm pH 0.00 to 14.00pH	0.00 to 20.00mS/cm 0.00 to 10.00ppt 0.00 to 14.00pH
Resolution	EC 1uS/cm TDS 1ppm pH 0.01pH	0 to +140.0°F both meters 0.01mS/cm 0.01ppt 0.01pH
Accuracy	Temp. 0.1°C & 0.1°F EC/TDS +/-2% Full S pH +/-0.05pH b Temp. +/-0.5°C or	
Compensation Calibration Electrode Dimensions Battery type and life	Temperature automatically compensated for in all ranges 1 or 2 points automatic for pH, 1 point automatic for EC/TDS HI73127 pH electrode cartridge included 163 x 40 x 26mm; 85 grams 4 x 1.5volt with auto-off after 8 minutes; 100 hours	
Accessories		
HI73127 HI7061 HI77400P HI70030P HI70031P HI70032P HI70038P	Spare/replacement pH electrode cartridge Electrode cleaning solution 5 sachets each of pH 4 and 7 calibration solution 25 sachets of 12.88mS/cm EC calibration solution 25 sachets of 1413uS/cm EC calibration solution 25 sachets of 1382ppm TDS calibration solution 25 sachets of 6.44ppt TDS calibration solution	