



PRODUCT-DETAILS

TC142
SADDLE SUPPORT BASE .9X.5IN NAT NYL



General Information	
Extended Product Type	TC142
Product ID	7TAG009880R0007
EAN	5414363058229
Catalog Description	SADDLE SUPPORT BASE .9X.5IN NAT NYL
Long Description	Saddle Support Mounting Base, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F), Length of 23.42mm (0.922 Inches), Width of 14.29mm (0.563 Inches), Height of 10.72mm (0.422 Inches), Mount with #10 Screw, Bulk Pack

Ordering	
EAN	5414363058229
UPC	786210822730
Country of Origin	United Kingdom (GB) United States (US)
Selling Unit of Measure	each

Container Information	
-----------------------	--

Package Level 1 Units	500 piece
Package Level 1 Width	12 in 305 mm
Package Level 1 Height	3 in 76 mm
Package Level 1 Depth / Length	15 in 381 mm
Package Level 2 Units	5000 piece
Package Level 2 Width	12.9 in 328 mm
Package Level 2 Height	13.6 in 345 mm
Package Level 2 Depth / Length	18 in 457 mm

Additional Information

Brand / Label	Ty-Rap
Color	Natural
Effective Date	19730511
Material	Nylon/Polyamide 6.6
Mounting Holes	#10
Mounting Type	Screw
Process Temperature Rating	-40 to +185 °F
Product Name	PLASTIC MOUNTING BASE
Product Type	Saddle Support Base
Special Functions	This mounting base provides a saddle for the wire run. Ty-Rap tie is threaded under bundle and tied in a usual manner.

Certificates and Declarations

Data Sheet, Technical Information	TC142
Declaration of Conformity - CE	9AKK107492A9840

Classifications

ETIM 6	EC000449 - Mounting base and -element for cable ties
ETIM 7	EC000449 - Mounting base and -element for cable ties
ETIM 8	EC000449 - Mounting base and -element for cable ties
UNSPSC	39121717
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5065 >> Cable tie mounts

Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties

