## ALPHA WIRE COMPANY CUSTOMER PRODUCT SPECIFICATION

		umber: 2461C l of 1 Pages		Issue: Issue Date Effective D	:	5 5/20/2005 8/1/2005
A.	Со	nstruction				<b>Diameters</b>
	1)	Component 1	2 X 1 COND			
		a) Conductor	22 (7/30) AWG TC			
		b) Insulation	0.008" Wall, Nom. Polyprop	oylene(PP)		0.046
		(1) Color(s)				
		Cond Color 1 BLACK	Cond Color 2 RED	Cond	Color	
	2)	Cable Assembly	2 Components Cabled			
	- 1	a) Twists:	9.6 Twists/foot (min)			
	3) Shield: Alum/Mylar Tape, 25% Overlap, Min					
		a) Foil Direction	Foil Facing Out			
		b) Drain Wire	22 (7/30) AWG TC			
	4)	Jacket	0.020" Wall, Nom.,PVC			0.136 (0.145 Max.)
		a) Color(s)	Gray, Black			
		b) Print	ALPHA WIRE-* P/N 2461C 2/C 22 AWG SHIELDED 75C (UL) TYPE CM LLXXXXXX CSA			
			TYPE CMG FT4 ROHS		~~~/	C3A
			* = Factory Code			
			[Note: Product may have c(UL) or	CSA markinas dei	pendin	a upon plant of manufacture.1
В.	Inc	lustry Approvals		<u>.</u>		<b>3</b> • [• • • • • • • • • • • • • • • • • •
	1)	UL	СМ	75°C		
	2)	CSA International	CMG	60°C		
			FT4			
	3)					
			All materials used in the ma			
			Directive 2002/95/EU regar			
			substances in electrical and			ent. Consult Alpha Wire's
	4)	Colifornia Droposition 65	web site for compliance Da			ature of this part most the
	4)	California Proposition 65.	The outer surface materials		anuia	icture of this part meet the
	Ph	ysical & Mechanical Prop	requirements of California I			
0.		Temperature Range	-20 to 75°C			
	2)	Bend Radius	10X Cable Diameter			
		Pull Tension	16.5 Lbs, Maximum			
D.		ectrical Properties	(For Engineering purposes	s only)		
		Voltage Rating	300 V <sub>RMS</sub>	, e,)		
		Mutual Capacitance	31 pf/ft @1 kHz, Nominal			
		Ground Capacitance	58 pf/ft @1 kHz, Nominal			
E.	Ótl		•			
		Packaging				
	-	a) 1000 FT				
		b) BOX 1000FT				

- c) 500 FT
- d) 100 FT

Although Alpha Wire Company ("Alpha") makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Alpha provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Alpha be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Alpha has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.