

Han 3A Push-In, male insert



Part number	09 20 003 5001
Specification	Han 3A Push-In, male insert
HARTING eCatalogue	https://b2b.harting.com/09200035001

Image is for illustration purposes only. Please refer to product description.

Identification

Category	Inserts
Series	Han A [®]

Version

Termination method	Push-In
Gender	Male
Size	3 A
Number of contacts	3
PE contact	Yes

Technical characteristics

Conductor cross-section	0.5 2.5 mm²
Rated current	10 A
Rated voltage conductor-earth	230 V
Rated voltage conductor-conductor	400 V
Rated impulse voltage	4 kV
Pollution degree	3
Insulation resistance	>10 ¹⁰ Ω
Limiting temperature	-40 +125 °C
Mating cycles	≥500

Material properties

Material (insert) Polycarbonate (PC)



Material properties

Colour (insert)	RAL 7032 (pebble grey)
Material flammability class acc. to UL 94	V-0
RoHS	compliant
ELV status	compliant
China RoHS	е
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Not contained

Specifications and approvals

Specifications	IEC 60664-1 IEC 61984
Approvals	CE
	UKCA

Commercial data

10
Germany
85366990
5713140434813
EC000438
27440205 Contact insert for industrial connectors