

# Product data sheet

Specifications

SQUARE D

Green Premium™



Safety switch, heavy duty, unfused, viewing window, NEMA 3R, 600V, 200A, 3 pole, neutral installed

VHU364NR

Product availability: Stock - Normally stocked in distribution facility

## Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	Neutral (factory installed)
Number Of Poles	3
Current Rating	200 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 3R galvanized steel
Motor Power Hp	15 hp at 240 V AC 50/60 Hz for 1 phase motors 60 hp at 240 V AC 50/60 Hz for 3 phase motors 50 hp at 480 V AC 50/60 Hz for 1 phase motors 125 hp at 480 V AC 50/60 Hz for 3 phase motors 50 hp at 600 V AC 50/60 Hz for 1 phase motors 150 hp at 600 V AC 50/60 Hz for 3 phase motors 40 hp at 250 V DC 50 hp at 600 V DC

## Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	4-wire (3PH + N)
Wire Size	AWG 6...250 kcmil copper or aluminium
Tightening Torque	275 lbf.in (31.07 N.m) 0.02...0.20 in <sup>2</sup> (13.3...127 mm <sup>2</sup> ) (AWG 6...250 kcmil)
Depth	8.506 in (216.05 mm)
Width	17.016 in (432.21 mm)
Height	28.94 in (735.08 mm)
Net Weight	44.00 lb(US) (19.96 kg)
Grounding Kit	Field installed kit available
Service Entrance	Suitable service entrance for USA Suitable service entrance for Mexico

## Environment

---

<b>Certifications</b>	UL listed file E2875
-----------------------	----------------------

## Ordering and shipping details

---

<b>Category</b>	US10DE100009
-----------------	--------------

---

<b>Discount Schedule</b>	0DE1
--------------------------	------

---

<b>Gtin</b>	3606485894850
-------------	---------------

---

<b>Returnability</b>	Yes
----------------------	-----

---

<b>Country Of Origin</b>	US
--------------------------	----

## Packing Units

---

<b>Unit Type Of Package 1</b>	PCE
-------------------------------	-----

---

<b>Number Of Units In Package 1</b>	1
-------------------------------------	---

---

<b>Package 1 Height</b>	19.38 in (49.2125 cm)
-------------------------	-----------------------

---

<b>Package 1 Width</b>	8.31 in (21.1137 cm)
------------------------	----------------------

---

<b>Package 1 Length</b>	30.00 in (76.2 cm)
-------------------------	--------------------

---

<b>Package 1 Weight</b>	54.45 lb(US) (24.7 kg)
-------------------------	------------------------

## Sustainability

**Green Premium™ label** is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

[Learn more about Green Premium >](#)

[Guide to assess a product's sustainability >](#)



Transparency RoHS/REACH

## Well-being performance

 Reach Free Of Svhc

 Rohs Exemption Information Yes

## Certifications & Standards

Reach Regulation [REACH Declaration](#)

Eu Rohs Directive Compliant  
[EU RoHS Declaration](#)

China Rohs Regulation [China RoHS declaration](#)

Environmental Disclosure [Product Environmental Profile](#)

Circularity Profile No need of specific recycling operations

California Proposition 65 WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to [www.P65Warnings.ca.gov](http://www.P65Warnings.ca.gov)