## Product data sheet

Specifications

#### SQUARE D





# Safety switch, heavy duty, fused, viewing window, NEMA 4X, 240V, 100A, 2 pole, ground lugs

VH223DSGL

Product availability: Stock - Normally stocked in distribution facility

#### Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Fusible disconnect
Factory Installed Neutral	Field installed kit available
Number Of Poles	2
Current Rating	100 A
Voltage Rating	250 V DC 240 V AC
Enclosure Rating	NEMA 4X stainless steel 304
Motor Power Hp	<ul> <li>7.5 hp at 240 V AC 50-60 Hz for 1 phase motors</li> <li>15 hp at 240 V AC 50-60 Hz for 3 phase motors</li> <li>15 hp at 240 V AC 50-60 Hz for 1 phase motors</li> <li>30 hp at 240 V AC 50-60 Hz for 3 phase motors</li> <li>20 hp at 250 V DC</li> </ul>

## Complementary

Short-Circuit Current	10 kA for H, K, J or R without fuse rejection clips 200 kA for R with fuse rejection clips
	200 kA for J
Fuse Туре	H or K
	R or J
Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	2-wire
Wire Size	AWG 12AWG 1/0 aluminium
	AWG 14AWG 1/0 copper
Tightening Torque	50 lbf.in (5.65 N.m) (AWG 1AWG 3/0)
	45 lbf.in (5.08 N.m) (AWG 6AWG 4)
	40 lbf.in (4.52 N.m) 0.01 in <sup>2</sup> (8.367 mm <sup>2</sup> ) (AWG 8)
	35 lbf.in (3.95 N.m) 0.000.01 in <sup>2</sup> (2.065.261 mm <sup>2</sup> ) (AWG 14AWG 10)
Depth	7.2 in (182.88 mm)
Width	9.336 in (237.13 mm)
Height	20.73 in (526.54 mm)
Net Weight	22.99 lb(US) (10.43 kg)
Grounding Kit	Factory installation

Suitable service entrance for USA Suitable service entrance for Mexico

#### Environment

Certifications

UL listed file E2875

## Ordering and shipping details

Category	US10DE100010
Discount Schedule	0DE1
Gtin	3606485893259
Returnability	Yes
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	11.50 in (29.21 cm)
Package 1 Width	7.50 in (19.05 cm)
Package 1 Length	22.62 in (57.467 cm)
Package 1 Weight	24.03 lb(US) (10.9 kg)

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Rohs Exemption Information

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov