# Product data sheet

Specifications







## Safety switch, heavy duty, unfused, viewing window, NEMA 3R, 600V, 100A, 3 pole, neutral installed

VHU363NRB

Product availability: Stock - Normally stocked in distribution facility

#### Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Non-fusible disconnect
Factory Installed Neutral	Neutral (factory installed)
Number Of Poles	3
Current Rating	100 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 3R galvannealed steel
Motor Power Hp	20 hp at 240 V AC 50/60 Hz for 1 phase motors 40 hp at 240 V AC 50/60 Hz for 3 phase motors 40 hp at 480 V AC 50/60 Hz for 1 phase motors 75 hp at 480 V AC 50/60 Hz for 3 phase motors 40 hp at 600 V AC 50/60 Hz for 1 phase motors 100 hp at 600 V AC 50/60 Hz for 3 phase motors 20 hp at 250 V DC 50 hp at 600 V DC

## Complementary

Mounting Type	Surface
Electrical Connection	Lugs
Wiring Configuration	4-wire (3PH + N)
Wire Size	AWG 12AWG 1/0 aluminium AWG 14AWG 1/0 copper
Tightening Torque	50 lbf.in (5.65 N.m) (AWG 1AWG 3/0) 45 lbf.in (5.08 N.m) (AWG 6AWG 4) 40 lbf.in (4.52 N.m) 0.01 in² (8.367 mm²) (AWG 8) 35 lbf.in (3.95 N.m) 0.000.01 in² (2.065.261 mm²) (AWG 14AWG 10)
Depth	7.019 in (178.28 mm)
Width	9.08 in (230.63 mm)
Height	22.103 in (561.42 mm)
Net Weight	18.39 lb(US) (8.34 kg)
Grounding Kit	Field installed kit available
Service Entrance	Suitable service entrance for USA Suitable service entrance for Mexico

## Environment

Certifications

#### UL listed file E2875

## Ordering and shipping details

Category	US10DE100009
Discount Schedule	0DE1
Gtin	3606485894713
Returnability	Yes
Country Of Origin	US

## **Packing Units**

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	22.62 in (57.4675 cm)
Package 1 Width	10.38 in (26.3525 cm)
Package 1 Length	7.00 in (17.78 cm)
Package 1 Weight	10.81 lb(LIS) (0 ka)

Package 1 Weight

19.84 lb(US) (9 kg)

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Yes

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

#### Well-being performance

Reach Free Of Svhc

Rohs Exemption Information

#### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov