





# Safety switch, heavy duty, fused, viewing window, Type 12, 600V, 200A, 3 pole, ground lugs

VH364AWKGL

Product availability: Stock - Normally stocked in distribution facility

### Main

Product	Single Throw Safety Switch
Duty Rating	Heavy duty
Device Application	Heavy application
Disconnect Type	Fusible disconnect
Factory Installed Neutral	Field installed kit available
Number Of Poles	3
Current Rating	200 A
Voltage Rating	600 V AC/DC
Enclosure Rating	NEMA 12 galvannealed steel
Motor Power Hp	50 hp at 480 V AC 50-60 Hz for 3 phase motors 125 hp at 480 V AC 50-60 Hz for 3 phase motors 60 hp at 600 V AC 50-60 Hz for 3 phase motors 150 hp at 600 V AC 50-60 Hz for 3 phase motors 40 hp at 250 V DC 50 hp at 600 V DC

## Complementary

Short-Circuit Current	10 kA for H, K, J or R without fuse rejection clips 200 kA for R with fuse rejection clips 200 kA for J	
Fuse Type	H or K R or J	
Mounting Type	Surface	
Electrical Connection	Lugs	
Wiring Configuration	3-wire	
Wire Size	AWG 6250 kcmil copper or aluminium	
Tightening Torque	275 lbf.in (31.07 N.m) 0.020.20 in² (13.3127 mm²) (AWG 6250 kcmil)	
Depth	9.02 in (229.11 mm)	
Width	17.01 in (432.05 mm)	
Height	28.93 in (734.82 mm)	
Net Weight	56.00 lb(US) (25.4 kg)	
Grounding Kit	Factory installation	
Service Entrance	Suitable service entrance for USA Suitable service entrance for Mexico	

## **Environment**

Certifications UL listed file E2875

## Ordering and shipping details

Category	US10DE100113	
Discount Schedule	0DE1	
Gtin	3606485894386	
Returnability	Yes	
Country Of Origin	US	

## Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	19.25 in (48.895 cm)
Package 1 Width	9.00 in (22.86 cm)
Package 1 Length	31.88 in (80.9625 cm)
Package 1 Weight	55.12 lb(US) (25 kg)



**Green Premium**<sup>TM</sup> **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

## Well-being performance



Reach Free Of Svhc



Rohs Exemption Information

Yes

### **Certifications & Standards**

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant EU RoHS Declaration
China Rohs Regulation	China RoHS declaration
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations
California Proposition 65	WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov