



PL Protecting Covers

Terminal Blocks Accessories



Features and Benefits

- Prohibit access to the screw clamps,
- Indicate live circuits.

Main Technical Data

Material Specifications	Insulating material	Polycarbonate	
	Flammability	V2	
	NF F 16 101		
Ambient temperature min/max	Service IEC 60068-2-1	-55 +110 °C	-67 +230 F
	Storage	-55 +110 °C	-67 +230 F
	Installing	-15 +40 °C	-23 +104 F

Ordering Details

PL Protecting Covers

Description	Type	Order Code	Pack ^(ing) pieces	Weight g (1 pce)
5.2 mm <i>0.205 in</i> spacing	Transparent <input checked="" type="checkbox"/>	PL5	20	1.50
6 mm <i>0.236 in</i> spacing		PL6	20	1.84
8 mm <i>0.315 in</i> spacing		PL8	20	2.55
10 mm <i>0.394 in</i> spacing		PL10	10	3.13
16 mm <i>0.630 in</i> spacing		PL16	10	4.60

PL Mounting Instructions



- The mounting of the PL does not require a screwdriver.
- The dismantling of the PL requires a screwdriver Dia.4 mm *0.160 in*, the screwdriver must be positioned in the cover centered hole.