



G2LU3AMF

USB 3.0 Extension Cable Male to Female 12 Inch

IOGEAR's USB 3.0 Type A Male to Female Cable is the perfect USB extension accessory just when you need it. Use it for any of your devices like hubs, keyboards, mice, docking stations, network hubs, bluetooth adapters and more.



Features

- Connect a USB 3.0 device up to 12 inches away
- Perfect for USB hubs, docking stations and peripherals
- USB 3.0 transfer rate of up to 5Gbps
- Up to 10x faster than USB 2.0
- Compatible with PC and MAC
- Backwards compatible with USB 2.0 and USB 1.1

Requirements

- USB Type A
- USB protocols: 1.1, 2.0 or 3.0

Package Contents

1 x G2LU3AMF



Specifications

FUNCTION	G2LU3AMF	DIMENSIONS	G2LU3AMF
Cable Length	12" (30cm)	POP Information	
Device Connection	USB 3.0 Type A	10" Peg Hook	14
Transfer Rate	Up to 5Gbps	6" Peg Hook	8
Operating System Support	Windows XP®, Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10 / Mac OS X v8.6 and above / Linux Kernel 2.4.20 and above / Google Chrome OS	Unit Dimensions	
		Height	12.8" (32.51cm)
		Length	0.67" (1.7cm)
		Depth	0.35" (0.9cm)
		Inner Pack	
		Height	4.45" (11.3cm)
		Length	9.45" (24cm)
		Width	8.56" (22.5cm)
		Inner Pack Qty.	12
		Unit Package Dimensions	
		Height	10.24" (26cm)
		Width	4.02" (10.2cm)
		Depth	0.30lb (0.75cm)
		Master Carton	
		Height	9.57" (24.3cm)
		Width	18" (45.72cm)
		Depth	10.24" (26cm)
		Master Carton Qty.	48
		Weight	
		Master Carton Wt.	5.73lb (2.6kg)
		Inner Pack Wt.	1.52lb (0.52 kg)
		Unit Pack Wt.	0.05 lb (0.02kg)
		Unit Wt.	0.04lb (0.018kg)