



GCS62HDPKIT

2-Port HDMI and DisplayPort Cable KVM Kit

IOGEAR's HDMI and DisplayPort KVM Solution enables effortless **control over two computers using a single USB keyboard, a USB mouse and a monitor** with HDMI connection or HDTV. This bundle is perfect for a home office or small / medium size business, as it offers the flexibility of choosing between HDMI and/or DisplayPort connections. Take advantage of your existing computers and use the **included DisplayPort adapters** to display your content on a large HDMI display or HDMI projector.



HDMI®
HIGH-DEFINITION MULTIMEDIA INTERFACE



Features

- Connect and control two HD or DisplayPort USB 2.0 interface computers with a single keyboard and mouse
- Full 1080p and up to 1920 x 1200 @ 60Hz
- Port switching via remote switch button, mouse or hotkeys
- Hotkeys allows independent KVM and audio switching between computers
- DisplayPort1.1a Compliant (with included adapters)
- Includes 2.1 stereo sound and microphone support
- USB 2.0 Peripheral Sharing via mouse port. Connect a powered USB Hub to expand your USB connectivity*
- USB mouse and keyboard emulation for error-free boot-up and instantaneous recognition when switching computers
- Power-On Detection – If one of the computers is powered off, it will automatically switch to the next powered-on computer
- Re-programmable hotkey activation for keyboards without a scroll lock key
- Keyboard emulation can be disabled to support gaming keyboard's special keys
- Mouse emulation can be disabled to support mice with special keys
- Digital Audio support
- HDCP Compliant
- Supports Windows® 7, 8.1, 10, 11, Mac OS® X 9.0+, Linux®, Unix and other USB supported systems
- Works with game consoles
- Mac and Sun keyboard support
- Firmware upgradeable
- All cables are included
- Plug-n-play; no software required
- DisplayPort to HD Adapters:
 - Converts your DisplayPort to HDMI so you can connect to your HDMI projector, TV or monitor
 - Works with computer systems using DisplayPort
 - Compliant with Displayport Specification 1.1a for both 1.62 Gbps and 2.7 Gbps
 - Support full DisplayPort link tracking
 - Supported resolutions:
 - Full HD 1080p
 - 1920x1200
 - Compliant with DVI 1.0 up to 1.65Gbps
 - Support interrupt request output for expansion function

www.iogear.com



- Support Deep Sleep Mode (suspend mode)

*Mouse emulation must be disabled for this feature to function correctly

Requirements

Console:

- 1 x HDMI display
- 1 x standard 104 key wired USB keyboard
- 1 x standard 2 or 3 button wired USB mouse

Computers:

- 1 x HDMI or DisplayPort
- 2 x USB ports

Operating Systems:

- Windows® 7, 8.1, 10, 11
- Mac OS® X 9.0+
- Oracle® Solaris
- Linux®, Unix and other USB supported systems*

**Additional drivers and support may be needed*

***IOGEAR's Display Emulation Technology provides the EDID support for Windows® 7*

Package Contents

- 1 x GCS62HU
- 2 x DisplayPort to HDMI Adapters
- 1 x Installation Guide
- 1 x Warranty Card



Specifications

DISTRIBUTOR	PART #
Ingram	8N7119
DH	GCS62HDPKIT
Synnex	4793098

FUNCTION	GCS62HDPKIT
Computer Connections	
Direct	2
Console Connectors	
Monitor	1 x HDMI Female
Audio	1 x 3.5mm Mini Stereo Jack Female (Green)
Microphone	1 x 3.5mm Mini Stereo Jack Female (Pink)
Keyboard	1 x USB Type A Female
Mouse	1 x USB Type A Female
CPU Connectors	
Monitor	2 x HDMI Male; 2 x DisplayPort Male (with adapter)
Audio	2 x 3.5mm Mini Stereo Jack Male (Green)
Microphone	2 x 3.5mm Mini Stereo Jack Male (Pink)
Keyboard	2 x USB Type A Male (Purple)
Mouse	2 x USB Type A Male (Black)
LEDs	
On Line	2 x Green
Emulation	
Keyboard	USB
Mouse	USB
Scan Interval	3, 5, 10 , 20 seconds (Default 5 seconds)
Environment	
Storage Temperature	-20~60°C
Operation Temperature	0~50°C
Humidity	0~80%; Non-condensing
Housing	
Case	Plastic
Video Resolution	1080p; 1920x1200
Port Selection	Remote Switch, Hotkey, and Mouse

DIMENSIONS	GCS62HDPKIT
POP Information	
10" Peg Hook	5
6" Peg Hook	3
Unit Dimensions	
Height	2.5" (6.35cm)
Depth	1" (2.54cm)



Length	3.125" (7.93cm)
--------	-----------------

Unit Package Dimensions

Width	6.5" (16.51cm)
-------	----------------

Height	9.25" (23.49cm)
--------	-----------------

Depth	2.75" (6.99cm)
-------	----------------

Master Carton

Width	16" (40.64cm)
-------	---------------

Height	9.5" (24.13cm)
--------	----------------

Depth	7.5" (19.05cm)
-------	----------------

Master Carton Qty.	6
--------------------	---

Weight

Master Carton Wt.	8.6lb (3.91kg)
-------------------	----------------

Unit Pack Wt.	1.3lb (0.59kg)
---------------	----------------

Unit Wt.	.94lb (0.43kg)
----------	----------------