



GPSU21

## USB 2.0 Print Server Adapter

IOGEAR's palm sized 1-port USB 2.0 Print Server allows any networked computer to share a USB printer. It complies with USB 2.0 specifications (backward compatible with USB 1.1 spec.), and provides users with an auto-sensing Ethernet port that works with either 10Base-T or 100Base-T networks.



### Features

---

- Easily connect your USB printer to a network
- Allows multiple computers to share one USB printer on the network
- Print from any computer on your network or from across the Internet
- Supports DHCP Client and multiple network protocols
- 10Base-T/100Base-T auto-sensing
- Supports Telnet and Web Management software

### Requirements

- Windows® 11, Windows® 10, Windows® 8.1, Windows® 8, Windows® 7
- Mac OS 10.3.9 or later
- Unix/Linux
- Printer with USB connection
- DHCP server on the network

### Package Contents

---

- 1 x 1-Port USB 2.0 Print Server
- 1 x CAT5 Patch Cable
- 1 x Power Adapter
- 1 x User Manual
- 1 x Warranty / Registration Card



## Specifications

---

FUNCTION	GPSU21
Cable Length	6 Feet
Network Protocol	IPX, TCP/IP, NETBUEI, APPLETALK, lpr, smb (Over IP)
Cable Type	CAT5
Network Interface	10/100Mbps RJ45
Printer Connection	USB 2.0, USB 1.1
Standards	IEEE 802.3 10Base-T; IEEE 802.3u 100Base-T; USB 2.0
Management	Web, Telnet, PSAdmin, SNMP
Operating Temperature	0°C to 45°C
Storage Temperature	-5°C to 65°C
Operating Humidity	0% to 70% relative humidity, non-condensing
Storage Humidity	0% to 80% relative humidity, non-condensing
DIMENSIONS	GPSU21
Unit Dimensions	
Height	1 in. (2.54 cm)
Length	2.5 in. (5.72 cm)
Width	2.4 in. (6.096 cm)
Unit Package Dimensions	
Height	5.5 in. (14cm)
Width	8 in. (20.32cm)
Depth	2.625 in. (6.6cm)
Master Carton	
Height	12.375 in. (31.41cm)
Width	8.875 in. (22.52cm)
Depth	17.5 in. (44.45cm)
Master Carton Qty.	12
Weight	
Master Carton Wt.	14.05 lb. (6.37 Kg)
Unit Pack Wt.	1.05 lb. 0.47 Kg)
Unit Wt.	0.12 lbs (0.05 Kg)