



GUD300

# USB 3.0 Universal Docking Station

IOGEAR'S USB 3.0 Universal Docking Station quickly and easily transforms your laptop, Ultrabook or Microsoft Surface® Pro tablet into a full-featured workstation. This universal dock is an all-in-one solution to the latest port-deficient laptops and tablets. It allows you to connect as many as 10 devices to your laptop through a single high speed USB 3.0 cable that offers speeds up to ten times faster than the previous USB 2.0 standard.



## Features

- Universal USB 3.0 Ultrabook / Laptop / Tablet\* Docking Station
- Dual Monitor support with DVI-I and HDMI outputs
- Resolution\*\*- HDMI: 2560x1440 single monitor only, DVI: 2048 x 1152, VGA (using supplied adapter): 1920x1200
- Integrated 2-port USB 3.0 and 4-port USB 2.0 Hub for external drives, cameras and phones
- Integrated Gigabit Ethernet port (RJ-45) - Supports 10/100/1000BASE-T
- Stereo audio with 3.5mm headphone output jack
- Microphone 3.5mm input jack
- Perfect for Workstations, Business, Home Offices and Entertainment Centers

\*Windows 8 Pro tablets (Microsoft Surface™ Pro, Surface™ Pro 2, etc.)

\*\*2560x1440 resolution requires connection via HDMI 1.4 cable and DVI output not used; maximum resolution with two monitors connected is 1920x1080 for both monitors

Microsoft and Surface are either registered trademarks or trademarks of Microsoft Corporation in the United States and/or other countries

DisplayLink driver does not work on MacOS 10.13.4 and above - [learn more](#)

## Requirements

### Hardware

- Computer or tablet with USB 3.0 or USB 2.0 port\*

\* USB 3.0 speeds are not available when connected to a USB 2.0 port.

### Operating System

- Windows® 7, Windows® 8, Windows® 8.1, Windows® 10, Windows® 11
- MAC OSX 10.6 or later

## Package Contents

1. 1 X GUD300 Universal Docking Station
2. 1 X USB 3.0 Super Speed Cable
3. 1 X HDMI to DVI Adapter
4. 1 X DVI to VGA Adapter
5. 1 X Software Installation CD
6. 1 X Quick Start Guide
7. 1 X AC Adapter
8. 1 X Warranty Card

**www.iogear.com**



## Specifications

FUNCTION	GUD300	DIMENSIONS	GUD300
Operating System Support	Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Mac OS X 10.6, 10.7, 10.8, 10.9, 10.10	POP Information	
		10" Peg Hook	2
USB Specification	USB 3.0	6" Peg Hook	1
		Unit Dimensions	
Resolution	HDMI: up to 2560x1440 (1 monitor connected via HDMI 1.4 cable), up to 2048x1152, 1920x1200 (2 monitors connected) / DVI: up to 2048x1152, 1920x1200 / VGA (using included adapter): up to 1920x1200	Height	1.4" (3.5cm)
		Length	8.8" (22.2cm)
		Depth	3.4" (8.7cm)
LAN Connection	Gigabit 10/100/1000Mbps	Unit Package Dimensions	
Power Adapter	Input: 100-240VAC @ 50/60Hz 2A Output: 12VDC @ 2A	Height	5.4" (13.7cm)
Connectors		Width	9.3" (23.5cm)
Audio Input	3.5mm mic input	Depth	3.5" (8.9cm)
Audio Output	Stereo audio with 3.5mm headphone output jack	Master Carton	
		Height	6.4" (16.2cm)
USB	(2) USB 3.0 / (4) USB 2.0 / (2) USB charge ports @ 1.5A output	Width	10" (25.4cm)
		Depth	11.5" (29.2cm)
LAN	RJ-45 Ethernet connector	Master Carton Qty.	3
Audio		Weight	
Audio Output	Supports 6 channel audio (5.1 surround) over HDMI	Master Carton Wt.	5.4lbs (2.4kg)
Console Connectors		Unit Pack Wt.	1.6lbs (.70kg)
Monitor	1 HDMI output & 1 DVI output (includes DVI to VGA & HDMI to DVI adapters)	Unit Wt.	.60lbs (.28kg)