



GUH274

USB 2.0 MicroHub™

IOGEAR's 4-Port USB 2.0 Hub provides 4 Hi-Speed USB 2.0 ports for your high-speed connectivity needs. This device is USB 2.0 certified and provides a data transfer rate of up to 480 Mbps (high speed).



Features

- 4 USB 2.0 ports for easy expansion
- Built-in USB cable for immediate connection
- Tuck-away cable design eliminates cable clutter
- Supports a data transfer rate of up to 480Mbps
- 40 Times faster than USB 1.1 products
- Guarantees 12Mbps bandwidth to each port for USB 1.1 devices
- Plug-n-Play, hot swappable
- Backward compatible with USB 1.1 specifications
- Supports Windows 98SE, 2000, ME, XP, Vista, 7, 8, 8.1 and Mac OS X or later version
- Overcurrent Protection
- LEDs allow for easy status monitoring
- 3 Year Limited Warranty

Requirements

For PC Users

- Windows 8/8.1, 10, 11
- Available USB 2.0 port
- Chrome Book
- Linux®, Unix and other USB supported systems*

*Additional drivers and support may be needed

For MAC Users

- Mac OS X 10.15 or later

Package Contents

- GUH274 - Hi-Speed USB 2.0 Hub
- Manual
- Power Adapter
- Warranty / Registration Card



Specifications

| FUNCTION | GUH274 | DIMENSIONS | GUH274 |
|--------------------------|---|-------------------------|---------------------|
| Housing | | Unit Dimensions | |
| Case | Plastic | Height | 0.5 in. (1.20 cm.) |
| LEDs | | Length | 3.5 in. (9.00 cm.) |
| Power On | 1 | Width | 1.5 in. (3.85 cm.) |
| Power Consumption | 5.0V, | Unit Package Dimensions | |
| Ports | 4 downstream | Height | 4.5 in. |
| Operating Temperature | 20 to 50 degrees (Celsius) | Width | 1.875 in. |
| Storage Temperature | 0 to 70 degrees (Celsius) | Depth | 7.675 in. |
| Operating System Support | Windows®, 98SE, 2000, ME, XP, MAC OS 8.6 or greater | Master Carton | |
| USB Specification | USB 1.1 and 2.0 compliant | Height | 10.5 in. |
| Transfer Rate | 480 Mbps | Width | 13.125 in. |
| Humidity | 20-80% RH, (Non Condensing) | Depth | 15.125 in. |
| Cable Length | 2.0 in. (5.0 cm.) | Master Carton Qty. | 24 |
| Power Connections | DC adapter (included) | Weight | |
| Cable Connections | | Master Carton Wt. | 14.7 lb. |
| Input | Hi-Speed USB Type A (female) | Unit Pack Wt. | 0.5 lb. |
| | | Unit Wt. | 0.1 lbs. (0.04 kg.) |