



GUH304

4 Port USB 3.0 Hub

While today's laptops are lighter and more compact than ever, that savings in size comes at the cost of fewer USB ports to connect your accessories. With the IOGEAR met(AL) Hub series you can instantly expand your USB connectivity with 4 SuperSpeed USB 3.0 ports, allowing you to reclaim your connectivity.



Features

- 4-Port SuperSpeed USB 3.0 Hub with up to 5Gbps data transfer rate
- Up to 10x faster than USB 2.0
- Aluminum housing designed to match Macbook computers
- Compatible with Mac and Windows
- Backwards compatible with USB 2.0, 1.1 and 1.0 devices*
- Supports overcurrent protection
- USB bus powered
- Plug-n-Play - no drivers or software required

*Device must be plugged into a USB 3.0 port in order to achieve SuperSpeed rates

Requirements

- Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10
- Mac OS X10.2+
- Linux
- USB 3.0 port

Package Contents

- 1 x GUH304
- 1 x Quick Start Guide
- 1 x Warranty Card



Specifications

FUNCTION	GUH304	DIMENSIONS	GUH304	
Operating System Requirements		POP Information		
Windows	Windows Vista®, Windows® 7, Windows® 8, Windows® 8.1, Windows® 10	10" Peg Hook	4	
		6" Peg Hook	2	
Mac	Mac OS X10.2+	Unit Dimensions		
Linux	Linux	Height	.75" (1.9cm)	
Connectors		Length	4.4" (11.2cm)	
USB	USB 3.0	Depth	1.42" (3.6cm)	
Power Output Rating		Inner Pack		
Total AC Power Outlet, 50/60Hz	DC5V@2A	Height	7" (17.8cm)	
		Length	8.5" (21.5cm)	
USB Specification	3.0, 2.0, 1.1	Width	10.3" (26.2cm)	
Transfer Rate	Up to 5Gbps	Inner Pack Qty.	6	
Ports	4 x USB 3.0	Unit Package Dimensions		
LEDs		Height	4.8" (12.2cm)	
Data	Blue	Length	5.7" (14.5cm)	
Operating Temperature	32 ~ 104F (0 ~ 40C)	Depth	2.6" (6.5cm)	
Storage Temperature	14 - 158F (-10 ~ 70C)	Master Carton		
Housing		Height	11.6" (29.5cm)	
Case	Aluminum alloy	Width	14.3" (36.5cm)	
		Depth	14.5" (36.8cm)	
		Master Carton Qty.		24
		Weight		
		Master Carton Wt.		12lb (5.4kg)
		Inner Pack Wt.		2.6lb (1.2kg)
		Unit Pack Wt.		.3lb (.14kg)
		Unit Wt.		.15lb (.07kg)