



GW4K30GH60

# Ultra-Fast 60GHz Wireless 4K HDMI® UHD Transmitter and Receiver Kit

The Ultra-Fast 60GHz Wireless 4K UHD Video Extender (GW4K30GH60) is an ultra-high-performance wireless AV solution that enables you to transmit 4K Ultra High Definition video and audio from an HDMI source over distances up to 50 feet with near-zero latency.



HDMI®  
HIGH-DEFINITION MULTIMEDIA INTERFACE



## Features

---

- Wirelessly send 4K UHD video from one HDMI source to one HDMI TV/Projector
- Extends signals up to 50 Ft. in-room
- Uncompressed audio and video at near-zero latency - ideal for gaming and streaming
- Resolutions up to 3840 x 2160 @30Hz
- Minimal interference with existing Wi-Fi devices via 60GHz wireless frequency
- Supports LPCM stereo audio format
- Plug-n-Play - Transmitter and receiver come pre-paired from factory
- Dedicated closed wireless system - Requires no Wi-Fi network
- Advanced wireless technology speeds to 18 Gbps
- LED status lights for source/display connections and wireless link
- Supports dual power option via USB or included AC adapter
- Compact mountable design for easy placement
- HDCP 2.2 compliant
- Supports 4K UHD

## Requirements

- Video source with HDMI output
- Video display with HDMI input
- AC power outlets or power USB port

## Package Contents

---

- 1 x GW4K30GH60 Transmitter
- 1 x GW4K30GH60 Receiver
- 2 x 3 Foot 2.0 HDMI Cables
- 2 x 5VDC/2A Switching Power Supply
- 1 x Quick Start Guide
- 1 x Warranty Card



## Specifications

FUNCTION	GW4K30GH60	DIMENSIONS	GW4K30GH60
Connectors		Unit Dimensions	
Video Input	HDCP 2.2 Support	Height	3"
Video Output	HDCP 2.2 Support	Length	1.125"
Power	5V/1A	Depth	4"
Video Resolution	3840 x 2160 @ 30Hz	Unit Package Dimensions	
Video Streaming	Uncompressed	Height	5.25"
Audio		Length	6"
Audio Output	LPCM Stereo	Depth	8"
Frequency Band	60 GHz	Master Carton	
Antenna Type	Printed Circuit Board	Height	14.5"
Environment		Width	17"
Operation Temperature	32~122°F (0~50°C)	Depth	6.75"
Storage Temperature	14~158°F (-10~70°C)	Master Carton Qty.	6
Humidity	10 - 90%	Weight	
Power Adapter	Input: 100~240 VAC/0.3A, Output: 5VDC/2A	Master Carton Wt.	13.60 lb
Housing		Unit Pack Wt.	2.10 lb
Case	Aluminum	Unit Wt.	0.50 lb (x2)
Warranty	1-Year		
Power Consumption	3W		