






| Pin No. | Cable TIA    |              |
|---------|--------------|--------------|
|         | 568A         | 568B         |
| 1       | white/green  | white/orange |
| 2       | green        | orange       |
| 3       | white/orange | white/green  |
| 8       | blue         | blue         |
| 7       | white/blue   | white/blue   |
| 4       | orange       | green        |
| 5       | white/brown  | white/brown  |
| 6       | brown        | brown        |

|            |            |
|------------|------------|
| cable Ø    | wire gauge |
| 5,1-10,1mm | AWG 26-23  |



|                                                                                                                                                                         |                                  |                                              |  |                                           |                |                        |      |                 |  |                    |  |                                                          |  |             |  |
|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------|----------------------------------|----------------------------------------------|--|-------------------------------------------|----------------|------------------------|------|-----------------|--|--------------------|--|----------------------------------------------------------|--|-------------|--|
|   |                                  | All Dimensions in mm<br>Original Size DIN A4 |  | Scale<br>1:1                              | Free size tol. |                        | Ref. |                 |  |                    |  |                                                          |  |             |  |
|                                                                                                                                                                         |                                  |                                              |  |                                           |                |                        | Sub. |                 |  |                    |  |                                                          |  |             |  |
|                                                                                      | All rights reserved              |                                              |  | Created by<br>HASSE                       |                | Inspected by<br>104125 |      | Standardisation |  | Date<br>2023-11-30 |  | State<br>Final Release                                   |  |             |  |
|                                                                                                                                                                         | Department EL PD                 |                                              |  |                                           |                |                        |      |                 |  |                    |  | Doc-Key / ECM-Nr.<br>100872772/UGD/003/E<br>500000258862 |  |             |  |
|                                                                                                                                                                         | HARTING<br><br>D-32339 Espelkamp |                                              |  | Title<br>M12-MD-CC-IDC-8P-XCOD-F-STR-SHLD |                |                        |      |                 |  |                    |  |                                                          |  |             |  |
|                                                                                                                                                                         |                                  |                                              |  | Type<br>TB                                |                | Number<br>21122832801  |      |                 |  |                    |  | Rev.<br>E                                                |  | Page<br>1/1 |  |