


PXP4002/001/02S Datasheet

Product Name // Pre-wired Flex Cable Connector - Right Angle - 1m - 2 Contacts - Socket

 [View Product Page](#)



// Product Description:	
- Pre-Wired Flex Cable Connector - Right Angle - Water and dustproof to IP68 when mated with compatible connector 4000 Series Buccaneer to blunt cut wire 1m Cable Length	2 Contacts - Socket - Sealing Cap available separately to maintain IP rating of unmated connectors - Mates with front and rear panel mounting connectors - and inline cable connectors

// General Information:	
Product Display Title:	Pre-Wired Flex Cable Connector
Product Family:	Circular Power Connectors
Product Series:	4000 Series Buccaneer
Approvals:	cUL, UL, VDE
Body Colour:	Black
Body Material:	Polyamide (PA)
Body Material Type:	Plastic Body
Cable Length:	1m
Contact Type:	Socket Contact
Coupling Type:	Bayonet Lock
Current Max:	13A
Diameter Over Coupling Ring Mm:	19.7mm
Flamability Rating:	UL94V-0
Function:	Flex Cable Connector
Ip Rating:	IP66, IP67, IP68
Max Operating Temperature:	+120°C
Min Operating Temperature:	-30°C
Number Of Contacts:	2 Contacts
Rohs Compliant:	Yes
Voltage Max:	600V

// Product PDF Links

 [4000 Series power connectors...](#)

// Product 3D CAD Model Links

 [PXP4002/001/02S3D CAD Model](#)