



ACPC

# 15 PSI-AF-CGRADE-MINI

ACPC 15 AF C



## Details

**Product Family:** ACPC

**Product Output:** Millivolt Compensated

**Product Grade:** CGRADE

**Media Isolated Coating:** No

**Package Type:** MINI

**Pressure Type:** Absolute

## Pressure Min: 0

**Pressure Max:** 15

**Units:** PSI

**Operating Temperature:** -25 to 85 C

**Supply Voltage:** 12 VS

## Honeywell PN:

**Supply Voltage:** 12 VS

### Package Drawing:

