



ACPC

4 INCH-GF-CGRADE-MINI

ACPCL 04 GF C



Details

Product Family: ACPC

Product Output: Millivolt Compensated

Product Grade: CGRADE

Media Isolated Coating: No

Package Type: MINI

Pressure Type: Gage

Pressure Min: 0

Pressure Max: 4

Units: IN H2O

Operating Temperature: -25 to 85 C

Supply Voltage: 12 VS

Honeywell PN:

Supply Voltage: 12 VS

Package Drawing:



