

Product Discontinuation

July 30th, 2024

CUI regrets to announce plans to obsolete the parts below effective immediately. We are not able to accept last time buy (LTB) orders.

Obsolete Part Number	Recommended alternatives
PDM1-S12-D15-S	PCN1-S12-D15-S
PDM2-S5-S15-S	PDQ2-D5-S15-S
PDS1-S12-S12-M-TR	PCN1-S12-S12-M-TR
PDS1-S12-S9-M-TR	None
PDS1-S15-S15-M-TR	PCN1-S12-S15-M-TR
PDS1-S24-D15-M-TR	PCN1-S24-D15-S
PDS1-S24-S12-M	PCN1-S24-S12-S
PDS1-S24-S15-M-TR	PCN1-S24-S15-S
PDS1-S24-S5-M	PCN1-S24-S5-S
PDS1-S3-S3-M-TR	None
PDS1-S3-S5-M-TR	PHP1-S3-S5-M-TR
PDS1-S5-D5-M-TR	PCN1-S5-D5-M-TR
PDS1-S5-S15-M-TR	PCN1-S5-S15-M-TR
PDS1-S5-S3-M-TR	PDQ2-D5-S3-S
PDS1-S5-S5-D	PCN1-S5-S5-M-TR, PCN1-S5-S5-S
PDS1-S5-S5-M	PCN1-S5-S5-M-TR
PDS1-S5-S5-S	PCSA1-S5-S5-S
PES1-S12-S12-M-TR	PCN1-S12-S12-M-TR
PQM1-S5-S15-M-TR	PCN1-S5-S15-M-TR
PYB10-Q24-D15-U	PDQ10-Q24-D15-D
PYB10-Q48-S12-U	PDQ10-Q48-S12-D
PDRA-120-24	None
PDRA-120-48	None
PDRB-45-12	None
PDRB-45-24	None
PDRB-45-48	None
PDRB-75-12	None

PDRB-75-24	None
PDRB-75-48	None
VGS-100B-12	None
VGS-100B-24	None
VGS-100B-48	None
VGS-150B-12	None
VGS-150B-24	None
VGS-150B-48	None
VGS-200B-12	None
VGS-200B-24	None
VGS-200B-48	None
VGS-250B-12	None
VGS-250B-24	None
VGS-250B-48	None
VGS-350B-12	None
VGS-350B-24	None
VGS-350B-30	None
VGS-350B-48	None
VGS-35B-12	None
VGS-35B-24	None
VGS-35B-48	None
VGS-50B-12	None
VGS-50B-24	None
VGS-50B-48	None
VGS-75B-12	None
VGS-75B-24	None
VGS-75B-30	None
VGS-75B-48	None
VSK-S10-12UA	PSK-10B-S12
VSK-S10-12UA-T	PSK-10B-S12
VSK-S10-15UA	PSK-10B-S15
VSK-S10-15UA-T	PSK-10B-S15
VSK-S10-24UA	PSK-10B-S24
VSK-S10-24UA-T	PSK-10B-S24
VSK-S10-3R3UA	None
VSK-S10-3R3UA-T	None

VSK-S10-5UA-T	PSK-10B-S5
VSK-S10-9UA	PSK-10B-S9
VSK-S10-9UA-T	PSK-10B-S9
SDI30-12-U2-P5	None
SDI30-12-U2-P5R	None
SDI30-12-U2-P6	None
SDI30-12-U2-P6R	None
SDI30-12-U-P5	None
SDI30-12-U-P5R	None
SDI30-12-U-P6	None
SDI30-12-U-P6R	None
SDI30-12-U-P14	None
SDI30-12-UC-P5	None
SDI30-12-UC-P5R	None
SDI30-12-UC-P6	None
SDI30-12-UC-P6R	None
SDI30-12-UC-P11	None
SDI30-12-UD2-P5	None
SDI30-12-UD2-P5R	None
SDI30-12-UD2-P6	None
SDI30-12-UD2-P6R	None
SDI30-12-UD-P5	None
SDI30-12-UD-P5R	None
SDI30-12-UD-P6	None
SDI30-12-UD-P6R	None
SDI30-12-UDC-P5	None
SDI30-12-UDC-P5R	None
SDI30-12-UDC-P6	None
SDI30-12-UDC-P6R	None
SDI30-15-U2-P5	None
SDI30-15-U2-P5R	None
SDI30-15-U2-P6	None
SDI30-15-U2-P6R	None
SDI30-15-U-P5	None
SDI30-15-U-P5R	None
SDI30-15-U-P6	None

SDI30-15-U-P6R	None
SDI30-15-U-P7	None
SDI30-15-UC-P5	None
SDI30-15-UC-P5R	None
SDI30-15-UC-P6	None
SDI30-15-UC-P6R	None
SDI30-15-UC-P7	None
SDI30-15-UD2-P5	None
SDI30-15-UD2-P5R	None
SDI30-15-UD2-P6	None
SDI30-15-UD2-P6R	None
SDI30-15-UD5-P5	None
SDI30-15-UD-P5	None
SDI30-15-UD-P5R	None
SDI30-15-UD-P6	None
SDI30-15-UD-P6R	None
SDI30-15-UDC-P5	None
SDI30-15-UDC-P5R	None
SDI30-15-UDC-P6	None
SDI30-15-UDC-P6R	None
SDI30-19-U2-P5	None
SDI30-19-U2-P5R	None
SDI30-19-U2-P6	None
SDI30-19-U2-P6R	None
SDI30-19-U-P5	None
SDI30-19-U-P5R	None
SDI30-19-U-P6	None
SDI30-19-U-P6R	None
SDI30-19-UC-P5	None
SDI30-19-UC-P5R	None
SDI30-19-UC-P6	None
SDI30-19-UC-P6R	None
SDI30-19-UD2-P5	None
SDI30-19-UD2-P5R	None
SDI30-19-UD2-P6	None
SDI30-19-UD2-P6R	None
SDI30-19-UD-P5	None

SDI30-19-UD-P5R	None
SDI30-19-UD-P6	None
SDI30-19-UD-P6R	None
SDI30-19-UDC-P5	None
SDI30-19-UDC-P5R	None
SDI30-19-UDC-P6	None
SDI30-19-UDC-P6R	None
SDI30-24-U2-P5	None
SDI30-24-U2-P5R	None
SDI30-24-U2-P6	None
SDI30-24-U2-P6R	None
SDI30-24-U-P5	None
SDI30-24-U-P5R	None
SDI30-24-U-P6	None
SDI30-24-U-P6R	None
SDI30-24-UC-P5	None
SDI30-24-UC-P5R	None
SDI30-24-UC-P6	None
SDI30-24-UC-P6R	None
SDI30-24-UD2-P5	None
SDI30-24-UD2-P5R	None
SDI30-24-UD2-P6	None
SDI30-24-UD2-P6R	None
SDI30-24-UD-P5	None
SDI30-24-UD-P5R	None
SDI30-24-UD-P6	None
SDI30-24-UD-P6R	None
SDI30-24-UDC-P5	None
SDI30-24-UDC-P5R	None
SDI30-24-UDC-P6	None
SDI30-24-UDC-P6R	None
SDI40-12-U2-P5	None
SDI40-12-U2-P5R	None
SDI40-12-U2-P6	None
SDI40-12-U2-P6R	None
SDI40-12-U-P5	None
SDI40-12-U-P5R	None

SDI40-12-U-P6	None
SDI40-12-U-P6R	None
SDI40-12-U-P7	None
SDI40-12-U-P10	None
SDI40-12-UC-P5	None
SDI40-12-UC-P5R	None
SDI40-12-UC-P6	None
SDI40-12-UC-P6R	None
SDI40-12-UD2-P5	None
SDI40-12-UD2-P5R	None
SDI40-12-UD2-P6	None
SDI40-12-UD2-P6R	None
SDI40-12-UD-P5	None
SDI40-12-UD-P5R	None
SDI40-12-UD-P6	None
SDI40-12-UD-P6R	None
SDI40-12-UDC-P5	None
SDI40-12-UDC-P5R	None
SDI40-12-UDC-P6	None
SDI40-12-UDC-P6R	None
SDI40-15-U2-P5	None
SDI40-15-U2-P5R	None
SDI40-15-U2-P6	None
SDI40-15-U2-P6R	None
SDI40-15-U-P5	None
SDI40-15-U-P5R	None
SDI40-15-U-P6	None
SDI40-15-U-P6R	None
SDI40-15-U-P11	None
SDI40-15-U-P51	None
SDI40-15-UC-P5	None
SDI40-15-UC-P5R	None
SDI40-15-UC-P6	None
SDI40-15-UC-P6R	None
SDI40-15-UD2-P5	None
SDI40-15-UD2-P5R	None
SDI40-15-UD2-P6	None

SDI40-15-UD2-P6R	None
SDI40-15-UD-P5	None
SDI40-15-UD-P5R	None
SDI40-15-UD-P6	None
SDI40-15-UD-P6R	None
SDI40-15-UDC-P5	None
SDI40-15-UDC-P5R	None
SDI40-15-UDC-P6	None
SDI40-15-UDC-P6R	None
SDI40-19-U2-P5	None
SDI40-19-U2-P5R	None
SDI40-19-U2-P6	None
SDI40-19-U2-P6R	None
SDI40-19-U-P5	None
SDI40-19-U-P5R	None
SDI40-19-U-P6	None
SDI40-19-U-P6R	None
SDI40-19-U-P11	None
SDI40-19-U-P51	None
SDI40-19-UC-P5	None
SDI40-19-UC-P5R	None
SDI40-19-UC-P6	None
SDI40-19-UC-P6R	None
SDI40-19-UD2-P5	None
SDI40-19-UD2-P5R	None
SDI40-19-UD2-P6	None
SDI40-19-UD2-P6R	None
SDI40-19-UD-P5	None
SDI40-19-UD-P5R	None
SDI40-19-UD-P6	None
SDI40-19-UD-P6R	None
SDI40-19-UDC-P5	None
SDI40-19-UDC-P5R	None
SDI40-19-UDC-P6	None
SDI40-19-UDC-P6R	None
SDI40-24-U2-P5	None
SDI40-24-U2-P5R	None

SDI40-24-U2-P6	None
SDI40-24-U2-P6R	None
SDI40-24-U3-P5	None
SDI40-24-U9-P5	None
SDI40-24-U-P5	None
SDI40-24-U-P5R	None
SDI40-24-U-P6	None
SDI40-24-U-P6R	None
SDI40-24-U-ST	None
SDI40-24-UC-P5	None
SDI40-24-UC-P5R	None
SDI40-24-UC-P6	None
SDI40-24-UC-P6R	None
SDI40-24-UD2-P5	None
SDI40-24-UD2-P5R	None
SDI40-24-UD2-P6	None
SDI40-24-UD2-P6R	None
SDI40-24-UD-P5	None
SDI40-24-UD-P5R	None
SDI40-24-UD-P6	None
SDI40-24-UD-P6R	None
SDI40-24-UDC-P5	None
SDI40-24-UDC-P5R	None
SDI40-24-UDC-P6	None
SDI40-24-UDC-P6R	None

If you have any questions concerning the discontinuation notice, please contact your local CUI Representative.