

USB2.0 COMMERCIAL (TYPE A AND B) -

UE27AC54100

OVERVIEW



OVERVIEW

DESCRIPTION

USB 2.0, Type A, Receptacle, Right Angle, 4 Pins, Shell Kink with Nickel Plating, 30µin Gold, Black Housing,

ENVIRONMENTAL COMPLIANCE

 [Drawing](#)

 [3D Model \(STP\)](#)

 [Product Specification](#)

DISTRIBUTOR STOCK CHECK

SYMBOL, FOOTPRINT & 3D

PART SPECIFICATION DETAIL

The information below is for reference only. For more technical details, refer to product specification and application specification.

Data Rate	480Mb/s	Gender	Receptacle
Height above Board	6.90mm (0.271in)	# of Contacts	4
Number of Decks	Single Deck	Plating Contact area	0.76µm (30.000µin) Gold
Plating Shell	1.27µm (50µin) Nickel	Product Types	A
Tail Length	2.84mm (0.112in)	Termination Style	Through Hole

3D VIEW

