



7		8	
REV	DESCRIPTION	SIGNATURE	DATE
AO	ORIGIN	Zhou Hao Yu	2024.04.26

TABLE A



Note:

1. Support 4 Lane DP2.1+USB2.0 & 2 Lane DP1.4+USB3.2
2. Support 4 Lane 8K@30Hz, 2 Lane 4K@60Hz video transmission ;
3. Support 10Gbps Data transmission ;
4. Backwards USB 2.0 & USB 1.1 ;
5. Support PD 60W Power Delivery 5m - 10m, 40W 15m

TABLE A

P/N	Model No	Customer P/N:	Length(mm)
	AOCUSB3C-705		5000+/-100
	AOCUSB3C-707		7500+/-100
	AOCUSB3C-710		10000+/-200
	AOCUSB3C-715		15000+/-250

10	Screw	4	PCS	 TOLERANCES UNLESS OTHERWISE STATED X. =±1 X.X =±0.25 X.X X =±0.1 TOOLING DECIMALS ANGLES X. ±0.3±1° X.X ±0.2±0.5° X. XX ±0.1±0.5°			
9	Clip	2	PCS				
8	SR black	2	PCS				
7	USB Type C A male shell(Upper)Black(Display)	1	PCS				
6	USB Type C A male shell(Bottom)Black(Source)	1	PCS				
5	USB Type C A male shell(Bottom)Black	2	PCS				
4	USB Type C PCBA (Display)	1	PCS				
3	USB Type C PCBA(Source)	1	PCS				
2	USB Type C A male nickel plated	2	PCS				
1	USB C Active Optical Cable Black TPE OD:6.5±0.3MM	TABLE A	mm				
ITEM	SPECIFICATIONS	Q' TY	UNIT				