Cable Ties

SRT Series Releasable Ties

Features and Benefits


Manufactured from a soft, tear-resistant thermoplastic polyurethane these ties have several unique features: UV and weather resistant, strong yet elastic, and suitable for temperatures as low as -40 degrees C. The SRT ties are releasable and reusable which is ideal for bundling cables in temporary applications such as musical events, theatres, cable harnesses.

Application

The SRT range offers solutions to numerous bundling applications. The soft, flexible material makes these ties particularly suitable for use on data and fibre-optic cables. The elasticity of the material makes them ideal for securing young trees to support poles, and other applications within the gardening and landscaping industry.



The Elasticity of the SRT ties makes them suitable for use in many applications.



Materi	ial Data	
RoHS	Material	Thermoplastic Polyurethane (TPU)
	Colour	Black (BK)
	Operating	-40 °C to +85 °C
	Temperature	
	Flammability	UL94 HB
		(halogenfre

Technical Table										
Article-No.	Туре	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)					
115-07189	SRT1807	180	7	45	57					
115-07269	SRT2607	260	7	79	57					
115-11269	SRT26011	260	11	55	123					
115-11349	SRT34011	340	11	90	123					
115-28589	SRT58028	580	28	150	360					
115-28889	SRT88028	880	28	240	360					





SRT ties available in small quantities.

Technical Table									
Article-No.	Туре	Length (L)	Width (W)	Bundle Ø max.	Min. Tensile Strength (N)	Pack Cont.			
115-07190	SOFTFIX® XS	180	7	45	57	16			
115-07270	SOFTFIX® S	260	7	79	57	12			
115-11270	SOFTFIX® M	260	11	55	123	8			
115-11350	SOFTFIX® L	340	11	90	123	6			
115-28590	SOFTFIX® XL	580	28	150	360	3			
115-28898	SOFTFIX® XXL	880	28	240	360	2			

All Dimensions in mm. Subject to technical changes.