



e.MMC-Based MCP PART

MTFC64GAZAQHD-AIT

Part Spec For

Capacity	64GB
Component Config	64G x8
Package Type	GREEN
I/O Voltage	1.8V
Pin Count	153-ball
PLP	NO
Part Status Code	Contact Factory
Family	MCP
Technology	MASSFLASH/CONTROLLER
Operating Temp	-40C to +85C



Documents

+ Data Sheet

+ Reach Statement

+ RoHS

+ Sim Model



[Products](#)

[Markets & industries](#)

[Partners](#)

[Sales and support](#)

[About](#)

[Investor relations](#)



[CONTACT US](#)

[Legal](#)

[Micron privacy notice](#)

[Suppliers](#)

[Terms and conditions of sale](#)

[Careers](#)

[Your privacy choices](#)



Micron Technology, Inc. All rights reserved. Information, products, and/or specifications are subject to change without notice. All information is provided on an "AS IS" basis without warranties of any kind. Drawings may not be to scale. Micron, the Micron logo, and all other Micron trademarks are the property of Micron Technology, Inc. All other trademarks are the property of their respective owners.

