

Temperature Calibrator

multicompPRO



Description

It is a hand-held temperature calibrator with stable performance and high accuracy. It can provide voltage, resistance, 10 kinds of the thermocouple and 4 kinds of RTD outputs. The thermocouple outputs are designed with automatic and manual cold junction temperature compensation. It also features automatic stepping and ramping. The 25% stepping function can be used for fast linearity detection, and the store/recall feature improves user efficiency.

Features

- Up to 0.05% output and measurement accuracy
- Compact and ergonomic design, easy to carry
- Solid and reliable, Suitable for on-site use
- Auto stepping and ramping output for fast linearity detection
- Save frequently-used settings for future use
- Adjustable backlight brightness
- Convenient battery replacement
- Slow /Fast/25% step ramp
- Backlight
- Auto power off
- Low battery indication
- Drop test: 1m

Electrical Specifications

Basic Functions	Type	Range	Best Accuracy
DC mV		1000mV	$\pm(0.05\% + 3)$
Resistance (Ω)		5000 Ω	$\pm(0.05\% + 2)$
Thermocouples	J	-20°C ~ 1200°C (-328°F ~ 2192°F)	0.7°C
	K	-200°C ~ 1370°C (-328°F ~ 2498°F)	1°C
	T	-200°C ~ 400°C (-328°F ~ 752°F)	0.8°C
	E	-200°C ~ 950°C (-328°F ~ 1742°F)	0.7°C
	R	-20°C ~ 1750°C (-4°F ~ 3182°F)	1.4°C
	S	-20°C ~ 1750°C (-4°F ~ 3182°F)	1.5°C
	B	600°C ~ 1800°C (1112°F ~ 3272°F)	1.4°C
	N	-200°C ~ 0 ~ 1300°C (-328°F ~ 2372°F)	0.9°C
	Wre325	0°C ~ 2000°C (32°F ~ 3632°F)	1.8°C
	Wre526	0°C ~ 2300°C (32°F ~ 4172°F)	1.8°C
RTDs	Pt10	-200°C ~ 850°C (-328°F ~ 1562°F)	$\pm(0.5\% + 6^{\circ}\text{C})$
	Pt100		$\pm(0.05\% + 0.6^{\circ}\text{C})$
	Cu50	-50°C ~ 150°C (-58°F ~ 302°F)	$\pm(0.05\% + 0.6^{\circ}\text{C})$
	Cu100		$\pm(0.05\% + 0.6^{\circ}\text{C})$

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO

General Characteristics

Power : 9V battery (6F22)
Product Net Weight : 410g
Product Size : 96mm × 193mm × 47mm (W × H × D)
Standard Warranty : 12 Months

Accessories	Qty.	Note
Operating Manual	1 piece	-
Test Leads	1 pair	Leads length: 900mm, Rod length: 128mm; Tip length: 16.8mm Safety level: CAT III 1000V/CAT IV 600V 10A
Alligator Clip		Neutral, Colour: Red + black
Battery	1 piece	9V Alkaline Battery(1604A), Non-rechargeable, Replaceable
Cloth bag		-

Part Number Table

Description	Part Number
Single Function Temperature Calibrator	MP780002

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.