



**Part Number :** [2064610400](#)  
**Product Description :** Micro-Fit+ Receptacle Housing, Dual Row, 4 Circuits, UL 94V-0, Glow-Wire Capable, Black  
**Series Number :** 206461  
**Status :** Active  
**Product Category :** Connector Housings



Documents & Resources


**Drawings**  
[Drawing 2064610400\\_sd.pdf](#)  
[Packaging Design Drawing 2064610000-PK-000.pdf](#)

**3D Models and Design Files**  
[3D Model 2064610400\\_stp.zip](#)

**Specifications**  
[Application Specification 2064600001-AS-000.pdf](#)  
[Product Specification 2064600000-PS-000.pdf](#)  
[Product Specification 2159530000-PS-000.pdf](#)  
[Test Summary 2064600000-TS-000.pdf](#)  
[Test Summary 2064600001-TS-000.pdf](#)  
[Test Summary 2159530000-TS-000.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2024)4144-DC (27 June 2024)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements  
- Eu RoHS  
- REACH SVHC

- Low-Halogen

#### Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

#### EU RoHS Certificate of Compliance

---

## Part Details

### General

Status	Active
Category	Connector Housings
Series	206461
Description	Micro-Fit+ Receptacle Housing, Dual Row, 4 Circuits, UL 94V-0, Glow-Wire Capable, Black
Application	Power, Wire-to-Board, Wire-to-Wire
Product Family	Micro-Fit+ Connector System
Product Name	Micro-Fit+
UPC	191130003068

### Agency

CSA	LR19980
UL	E29179

### Physical

Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	Yes
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.528/g

Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	3.00mm
Pitch - Termination Interface	3.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +125°C

---

## Mates With / Use With

### Mates with Part(s)

Description	Part Number
Micro-Fit+ Vertical, Dual Row, Through Hole Headers	<u>206832</u>
Micro-Fit+ Right-Angle, Dual Row, Through Hole Headers	<u>212528</u>
Micro-Fit+ Dual Row Surface Mount Headers	<u>218216</u>
Micro-Fit+ Versa Color Vertical, Dual Row, Through Hole Headers	<u>224246</u>
Micro-Fit+ Dual Row Plug Housings	<u>215922</u>

### Use with Part(s)

Description	Part Number
Micro-Fit+ Female Crimp Terminals	<u>206460</u>
Micro-Fit+ Terminal Position Assurance (TPA) Retainers	<u>206462</u>