


MALLORY Mallory Sonalert Products, Inc.	Part #: JTC120-RY-CD
Sales Outline Drawing	Revision: A

Specifications:

Stack Number:	1	2			
LED Color:	RED	YELLOW			
LED Operation:	Continuous	Continuous			
Connection Wires:	Red and Brown	Yellow and Brown			
LED Current Draw:	<210 mA	<230 mA			
Rated Voltage:	120 VAC				
Operating Voltage:	90-120 VAC				
Total Max Current:	<440mA				
Operating Temperature:	-25° ~ +60°C				
Lens Color:	Transparent - matching LED stack color				
Material:	Lexan CFR7431				
Mounting Method:	Direct Mount using 1/2" NPT Stainless Steel Pipe and Nut				
Weight Typical (g):	215				
NEMA 12:	Approved				
Options:	Please contact factory.				

Dimensions: Inches (mm) **cUL Recognized** **ROHS Compliant**

PATENT NUMBER(S) 10309594 D898600



LED OPERATION: CONNECT STACK COLOR WIRE TO POWER AND BROWN WIRE TO POWER.