



Features:

- International Style: 7
- Product Type: ESD Rubber Tweezers
- Body Material: Anti-Magnetic Anti-Acid Stainless Steel (SA)
 - Coating/Finish: Sandblasted
- Handle Material: ESD safe thermoplastic rubber (DR)
- Tip Description: curved, very fine, sharp
- **Description:** The 7-SA-DR high precision tweezers are suitable to delicate applications which require holding a small component firmly while granting maximum visibility. The curved geometry provides maximum visibility and increased ergonomics. The ESD rubber grip provides the tweezers with ESD properties combined with an ergonomic handle suitable to electronic components handling and to clean room use.


Tweezer Dimensions:

OAL: 120.0 mm — 4.724"
Width: 12.5 mm — 0.492"
Height: 15.0 mm — 0.591"

Tip Dimensions:

Width: 0.16 mm — 0.006"
Thickness: 0.09 mm — 0.004"

Tip Details:



PRECISION STAINLESS STEEL TWEEZER, ESD RUBBER GRIP,

Unless otherwise noted, tolerance is ±10%.

CURVED FINE SHARP TIP, STYLE 7

Made in Switzerland

Specifications and procedures subject to change without notice.



2860 CORDELIA RD STE 230, FAIRFIELD CA, 94534

PHONE: (909) 627-2453 WEBSITE: TronexTools.com DRAWING NUMBER 7-SA-DR July 2024