

Product Datasheet

Product code: **PC2550E**

Product type: TEK-ME Carbon Steel Hand tools

Made in: Italy

Description: The PC2550E is an angled flush cutter. Its medium size (2,5mm thick) allow the cutting of bigger electronic components than in the micro line. In addition, its 50° angled head provides excellent visibility when used in either vertical or horizontal position. The cutters are equipped with an ESD and ergonomic handle which allows an excellent grip, suitable to environments and to components susceptible to electrostatic discharges.

Head description: Angled Medium, Shear

Cutting edges: Full-Flush

Cutting capacity: soft wire 1.3 mm (16 AWG)

Body material: Carbon Steel (C70)

Body finishing: Phosphated

Picture:



Dimensions:	OAL (A)	135.0 mm – 5.315 inch
	Width	80.0 mm – 3.150 inch
	Height	15.0 mm – 0.591 inch

Head dimensions:	Width (C)	14.0 mm – 0.551 inch
	Thickness (D)	4.0 mm – 0.157 inch
	B	10.0 mm – 0.394 inch
	F	0.8 mm – 0.031 inch

