

Product Information

95 16 165

Cable Shears



⚡ 1000 V

- Clean and smooth cut without crushing and deformation
- Easy cutting with one-hand operation
- Adjustable bolted joint, self-retaining screw
- Cuts multi-core stranded copper and aluminium cables up to Ø 15 mm (50 mm²)
- Not suitable for steel wire and hard drawn copper conductors
- Precision-ground, hardened blades
- With guard

General	
Article No.	95 16 165
EAN	4003773039648
Shears	chrome-plated
handles	insulated with multi-component grips, VDE-tested
Weight	262 g
Dimensions	165 x 47 x 21 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacity copper cable, multiple-stranded	50 mm²
Cutting capacity copper cable, multiple-stranded	Ø 15 mm
AWG	1 / 0
VDE tested	yes

Technical changes and errors excepted

