

Fire Retardant PVC Foam Tape **multicomp**^{PRO}

**RoHS
Compliant**



Description

A medium density, closed cell PVC foam, fire retardant sealant. Coated on one side with a strong acrylic pressure sensitive adhesive. A water and weather seal for heavy duty sealing and cushioning applications.

Applications

- Truck Cab and body seals
- Truck trailer side walls
- Outdoor lighting fixtures
- Appliance seals
- Metal building seals
- Metal to metal joints

Technical Data

Shore Hardness	: 30 Shore
Density	: 135-200 kg/m ³
Compress by 30%	: 2-5 N/cm ²
Deflection by 30%	: 1-3 N/cm ²
Water Absorption	: 3% Max
Tensile	: 24 N/cm ²
Elongation	: 105% Max
Temperature Range	: -30°C to +70°C
Min. Application Temperature	: +5°C

Benefits

- Certified to Class B2 of DIN 4102-01, 05/98
- 30% compression assures weather tight seal.
- Good resistance to oxygen, weather & fungi.
- Good chemical resistance.
- Excellent long term ageing/uv resistance.
- Effective vibration dampening.
- Abrasion resistant
- Removable paper liner prevents stretching during application.
- Works with mechanical fastenings
- Resists distortion from drilling, riveting etc
- Economical

Limitations

PVC foam contains plasticisers, therefore not suitable for use on polycarbonate.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicomp^{PRO}

Fire Retardant PVC Foam Tape

multicompPRO

Production Advantages

- Clean and simple to use.
- Quick and efficient application.
- Consistent adhesive coating thickness.
- Consistent adhesion performance.
- Instant adhesion.
- No hazardous fumes.
- No drying or curing times.
- Ready for the next part of the application process.
- No contamination of other surfaces.
- This product in any width roll, converted to an exact tolerance and dispatched within a few days
- Pads, die cut gaskets, sheets and special laminations also available

Product Availability

Colour	: Black
Width	: 6mm, 12mm and 19mm (Tolerance ± 1 mm)
Thickness	: 3mm, 4.5mm, and 6mm (Tolerance $\pm 15\%$)
Release Liner	: Paper

Part Number Table

Description	Size Width×Thickness×Length	Part Number
Tape Foam Sealer, Black	6mm×3mm×25m	PPC116
	12mm×4.5mm×15m	PPC117
	19mm×4.5mm×15m	PPC118
	19mm×6mm×12m	PPC119

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
sg.element14.com/b/multicomp-pro

multicompPRO