Specifications

Green Premium



# PC box IP66 IK08 RAL7035 Int.H175W150D100 Ext.H193W164D105 opaque PC cover H40

Local distributor code: 387531768

NSYTBP191610H

#### EAN Code: 3606480165672

#### Main

| Range               | Thalassa                               |
|---------------------|--|
| Product name        | Thalassa TBP                           |
| Device application  | Multi-purpose                          |
| Category            | Industrial box                         |
| Height              | 192 mm                                 |
| Width               | 164 mm                                 |
| Depth               | 105 mm                                 |
| Internal height     | 175 mm                                 |
| Internal width      | 150 mm                                 |
| Internal depth      | 100 mm                                 |
| enclosure mounting  | Wall mounted                           |
| Device composition  | 1 body                                 |
|                     | 1 cover                                |
|                     | 4 cover screw                          |
| Body type           | One piece moulded                      |
| Type of front cover | High plain cover                       |
| Cover fixing        | Plastic screws                         |
| Lock type           | Captive screw flat outside sealed area |
| Removable parts     | Cover by captive screws                |
|                     |  |

### Complementary

| Material                    | Polycarbonate   |  |
|-----------------------------|---|--|
| Colour                      | Grey (RAL 7035)   |  |
| Standards                   | UL 508 A<br>IEC 62208                                       |  |
| Product certifications      | TÜV<br>UL   |  |
| Electrical insulation class | Class II  |  |
| Mounting location           | Outdoor (with canopy or shelter and anticondensation valve) |  |
| Product weight              | 0.62 kg   |  |

#### Environment

IP degree of protection

IP66 conforming to NEMA 4.4X

| IK degree of protection             | IK08 conforming to IEC 62262 |
|-------------------------------------|------------------------------|
| Fire resistance                     | 960 °C                       |
| Ambient air temperature for storage | -1560 °C                     |
| Operating temperature               | -2580 °C                     |

# **Packing Units**

| •                            |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 12.45 cm |
| Package 1 Width              | 17.02 cm |
| Package 1 Length             | 21.08 cm |
| Package 1 Weight             | 1.24 kg  |
| Unit Type of Package 2       | CAR      |
| Number of Units in Package 2 | 17       |
| Package 2 Height             | 40 cm    |
| Package 2 Width              | 41 cm    |
| Package 2 Length             | 61 cm    |
| Package 2 Weight             | 10.94 kg |
| Unit Type of Package 3       | PAM      |
| Number of Units in Package 3 | 425      |
| Package 3 Height             | 215 cm   |
| Package 3 Width              | 100 cm   |
| Package 3 Length             | 120 cm   |
| Package 3 Weight             | 287 kg   |
|                              |          |

# **Contractual warranty**

Warranty

18 months

## Sustainability Screen

**Green Premium<sup>TM</sup> label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO<sub>2</sub> products.

**Guide to assessing product sustainability** is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

### Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

#### **Certifications & Standards**

| Reach Regulation         | REACh Declaration   |
|--------------------------|---|
| Eu Rohs Directive        | Pro-active compliance (Product out of EU RoHS legal scope)<br>EU RoHS Declaration           |
| China Rohs Regulation    | China RoHS declaration<br>Pro-active China RoHS declaration (out of China RoHS legal scope) |
| Environmental Disclosure | Product Environmental Profile   |
| Circularity Profile      | End of Life Information   |

### Product datasheet

Image of product / Alternate images

Alternative

