Specifications

, Green Premium™



Mounting plate in galvanized steel, thickness 15 mm For boxes of H175W150 mm

Local distributor code: 387529068

NSYAMPM1916TB

EAN Code: 3606480166082

Main

Range	Thalassa
Accessory / separate part category	Mounting accessory
Product or component type	Mounting plate
Device application	Multi-purpose
Enclosure nominal dimensions	-
Mounting location	Back studs
Mounting plate description	Plain
Range compatibility	Thalassa Thalassa TBS Thalassa Thalassa TBP
Device composition	1 mounting plate
Material	Galvanised steel

Complementary

Fixing mode	By screws - screw type M4 self tapping - on back studs location
Height	Nominal: 192 mm Real: 140 mm
Width	Nominal: 164 mm Real: 1685 mm
Thickness	1.5 mm
Net weight	0.1 kg

Packing Units

•	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	0.200 cm
Package 1 Width	14.000 cm
Package 1 Length	17.000 cm
Package 1 Weight	263.000 g
Unit Type of Package 2	CAR
Number of Units in Package 2	10
Package 2 Height	4.000 cm
Package 2 Width	16.000 cm
Package 2 Length	18.500 cm

Package 2 Weight	2.600 kg
Unit Type of Package 3	РАМ
Number of Units in Package 3	480
Package 3 Height	23.000 cm
Package 3 Width	100.000 cm
Package 3 Length	120.000 cm
Package 3 Weight	138.000 kg

Contractual warranty

Warranty

18 months

Sustainability Screen Premium

Green PremiumTM label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency RoHS/REACh

Well-being performance

Reach Free Of Svhc
Toxic Heavy Metal Free
Mercury Free
Rohs Exemption Information Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
China Rohs Regulation	China RoHS declaration Pro-active China RoHS declaration (out of China RoHS legal scope)
Environmental Disclosure	Product Environmental Profile
Circularity Profile	No need of specific recycling operations