



5in7 small touchscreen display front module Backlight LED Color TFT LCD

Local distributor code: 398067946

HMIS85

EAN Code: 3595864149059

Main

Range of product	Harmony SCU	
Product or component type	Small touchscreen display HMI	
Display size	5.7 inch	
Pixel resolution	320 x 240 pixels QVGA	

Complementary

Display type	with backlit LED colour TFT LCD
Touch panel	Analogue
Backlight lifespan	50000 hours with 65536 colours
Brightness	16 levels via touch panel
View angle horiz x vert	60° left 60° right 40° top 60° bottom
Character font	Korean Chinese (simplified Chinese) ASCII Taiwanese (traditional Chinese) Japanese (ANK, Kanji)
Height	129.15 mm
Width	163 mm
Depth	129.4 mm
Net weight	0.405 kg

Environment

Product certifications UKCA

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	18.4 cm
Package 1 Width	5.6 cm
Package 1 Length	26.7 cm
Package 1 Weight	660 a

Contractual warranty

Warranty

18 months



Green PremiumTM **label** is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO₂ products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >





Transparency RoHS/REACh

Well-being performance



Mercury Free



Rohs Exemption Information


Yes

Certifications & Standards

Reach Regulation	REACh Declaration	
Eu Rohs Directive	Pro-active compliance (Product out of EU RoHS legal scope)	
China Rohs Regulation	China RoHS declaration	
Environmental Disclosure	Product Environmental Profile	
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins	
Circularity Profile	End of Life Information	


Dimensions Drawings

Dimensions of 5.7-inches Display Module




Mounting and Clearance

Mounting Without an Anti-Rotation Tee



Α	B (1)	B (2)
22.50 ^{0/-0.30} mm	1.56 mm	36 mm
(0.88 ^{0/-0.01} in.)	(0.060.23 in.)	(0.110.23 in.)

Mounting With an Anti-Rotation Tee



С	D
	4 ^{0/-0.20} mm (0.15 ^{0/-0.007} in.)

Image of product / Alternate images

Alternative







