



Sample photo

Order symbol: CAB ABSQ 303017 G
Product nbr: 8183348
Description: Cabinet, ABS
Remarks: Grey cover

EAN: 6418074011299
El. number:
Finland: 3424308
Electric No. Italy: 7671030
Electric No. Sweden: 8183348

Including: Base with screws for mounting plate/DIN-rail, internal corner plugs, cover with PUR gasket and CS 12137 cover screws.

Dimensions:	Length	Width	Height
mm:	300	300	170
inch:	11.8	11.8	6.7

Materials:	
Material:	ABS
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	RAL 5023
Gasket material:	Polyurethane

Temperatures:	
Temperature °C (short term):	-40 ... 80 °C
Temperature °C (continuous):	-40 ... 60 °C
Temperature °F (short term):	-40 ... 175 °F
Temperature °F (continuous):	-40 ... 140 °F

Accessories:	
EKIV 33	Mounting plate

Accessories:	
EKIV 27	DIN-35 Mounting rail
FP A 33	Swing-out door/Front plate
MB 12225 AL	Swing door set
FP 12-33	Front plate
FP 12x2-33	Front plate
DRF 33	DIN rail frame set
PAT 12040	Hinge set

Rating:	
Ingress Protection (EN 60529): IP66/IP67	
Impact Resistance (EN 62262): IK08	
Electrical insulation: Totally insulated	
Halogen free (DIN/VDE 0472, Part 815): 1	
Flammability Rating: UL 94 HB	
Glow Wire Test (IEC 695-2-1) °C: 650	
NEMA Class: NEMA 1, 4, 4X, 12, 13	

