

FMF 17 Set



Sample image

Order symbol : FMF 17 Set

Product nr : 3576152

Description : Suitable for flange size 2, IP55

Remarks : Bushing points: 9 x 18 mm – 30 mm / 10 mm – 14 mm 4 x 10 mm – 15 mm 4 x 5 mm – 10 mm

EAN : 6418074320803

El. number :

- Finland : 3424744
- Denmark : 8212052699
- Sweden : 2600085

3576152_FIBOX_FMF_17_DIM

Dimensions :	Height	Width	Depth
mm :	84	216	24
inch :	3.31	8.5	0.94

Materials :

Material :	TPE
Gasket material :	TPE

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175

Ratings :

Ingress protection (EN 60529):	IP65;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	-
Flammability Rating :	UL 94 V0