



Pushing Performance  
Since 1945

# ix Type B OM 10xAWG26 PUR 5.0m



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                             |
|--------------------|---------------------------------------------------------------------------------------------|
| Part number        | 33 48 323 2A21 050                                                                          |
| Specification      | ix Type B OM 10xAWG26 PUR 5.0m                                                              |
| HARTING eCatalogue | <a href="https://b2b.harting.com/33483232A21050">https://b2b.harting.com/33483232A21050</a> |

## Identification

|               |                                      |
|---------------|--------------------------------------|
| Category      | System cabling                       |
| Series        | HARTING ix Industrial®               |
| Element       | Cable assemblies                     |
| Specification | Pre-assembled on both sides          |
| Connector 1   | HARTING ix Industrial® PushPull IP20 |
|               | Type B                               |
|               | Overmoulded                          |
|               | IDC termination                      |
| Connector 2   | HARTING ix Industrial® PushPull IP20 |
|               | Type B                               |
|               | Overmoulded                          |
|               | IDC termination                      |
| Type of cable | Copper cable (round)                 |

## Version

|                    |              |
|--------------------|--------------|
| Cable length       | 5 m          |
| Number of cores    | 10           |
| Core structure     | 5x 2x AWG 26 |
| Number of contacts | 10           |

## Technical characteristics

|               |         |
|---------------|---------|
| Rated current | 1.5 A   |
| Rated voltage | 50 V AC |
|               | 60 V DC |



**Pushing Performance**  
Since 1945

## Technical characteristics

|                      |                        |
|----------------------|------------------------|
| Limiting temperature | -40 ... +80 °C unmoved |
|                      | -5 ... +80 °C moved    |

## Material properties

|                                      |                    |
|--------------------------------------|--------------------|
| Material (cable)                     | PUR (polyurethane) |
| Colour (cable)                       | Grey               |
| RoHS                                 | compliant          |
| ELV status                           | compliant          |
| China RoHS                           | e                  |
| REACH Annex XVII substances          | Not contained      |
| REACH ANNEX XIV substances           | Not contained      |
| REACH SVHC substances                | Not contained      |
| California Proposition 65 substances | Not contained      |

## Specifications and approvals

|                |                 |
|----------------|-----------------|
| Specifications | EN 50363-10-2   |
|                | IEC 61076-3-124 |

## Commercial data

|                                |                                         |
|--------------------------------|-----------------------------------------|
| Packaging size                 | 1                                       |
| Net weight                     | 305 g                                   |
| Country of origin              | Latvia                                  |
| European customs tariff number | 85444290                                |
| GTIN                           | 5713140333260                           |
| eCl@ss                         | 27060311 Assembled sensor actuator-line |