


AOUS5/020 Datasheet

[View Product Page](#)

Product Name // USB 3.2 Gen1 Active Optical Cable, A male to Micro-B male drag chain jacket with screws, right angle 20m



// Product Description:

- USB 3.2 Gen1 Active Optical Cable, A male to Micro-B male drag chain jacket with screws, right angle
- Cable length 20m
- 90-degree angle design for limited space connections
- Braided cable jacket for drag chain applications
- Up to 5Gbps

// General Information:

Product Display Title:	USB 3.2 Cable
Product Family:	Data Connectors
Product Series:	AO Series USB
Body Colour:	Black
Body Material:	Zinc Alloy
Body Material Type:	Metal
Cable Length:	20m
Contact Type:	Plug Contact
Data Cable Type:	USB 3.2 Gen 1
Durability:	1000
Fibre Mode:	Multimode
Flamability Rating:	VW-1
Function:	USB 3.2 Cable
Max Operating Temperature:	50°C
Min Operating Temperature:	0°C
Rohs Compliant:	Yes
Sheath Colour:	Black
Sheath Material:	PVC
Voltage Max:	5.5V

// Product PDF Links

[AO Series USB product data](#)

// Product 3D CAD Model Links

[AOUS5/0203D CAD Model](#)



Have a question or project enquiry
you'd like to talk to us about?



[Click Here To Contact Us](#)