



## HDRZ40-BL-SW

- hygienic design
- with or without latching
- small body illuminable

## Data

### Ordering data

|                               |               |
|-------------------------------|---------------|
| Product type description      | HDRZ40-BL-SW  |
| Article number (order number) | 103039516     |
| EAN (European Article Number) | 4030661617428 |
| eCl@ss number, version 12.0   | 27-37-12-12   |
| eCl@ss number, version 11.0   | 27-37-12-12   |
| eCl@ss number, version 9.0    | 27-37-12-12   |
| ETIM number, version 7.0      | EC001038      |
| ETIM number, version 6.0      | EC001038      |

### Approvals - Standards

|              |                |
|--------------|----------------|
| Certificates | hygiene tested |
|--------------|----------------|

### General data

|           |                                                     |
|-----------|-----------------------------------------------------|
| Standards | EN IEC 60947-5-1<br>EN IEC 60947-1<br>DIN EN 1672-2 |
| Versions  | Front plate mounting                                |
| Design    | Round                                               |

|                                 |                         |
|---------------------------------|-------------------------|
| Sealing type                    | Membrane<br>Lip gaskets |
| Material of the operators       | Plastic                 |
| Material of the front ring      | stainless steel         |
| Material of the bellows         | Silicone                |
| Colour of the operating element | Black                   |
| Colour of the front ring        | Silver                  |
| Colour of the bellows           | Blue                    |

### General data - Features

|                            |     |
|----------------------------|-----|
| Mounting flange            | Yes |
| Probing possible           | No  |
| Latching                   | Yes |
| Fully insulated            | Yes |
| Number of switch positions | 1   |

### Mechanical data

|                                    |             |
|------------------------------------|-------------|
| Actuating stroke                   | 5.5 mm      |
| Mounting                           | central nut |
| Tightening torque of nuts, maximum | 4 Nm        |

### Mechanical data - Dimensions

|                                        |                                                      |
|----------------------------------------|------------------------------------------------------|
| Height                                 | 20 mm                                                |
| Mounting height                        | 38 mm                                                |
| Note (Mounting height)                 | Height in front of the front panel.                  |
| Mounting depth                         | 48 mm                                                |
| Note (Mounting depth)                  | Depth behind front panel including a contact element |
| Diameter of touch surface              | 40 mm                                                |
| diameters for the actuating heads      | 45 mm                                                |
| Mounting diameter                      | 22.3 mm                                              |
| Thickness, of the front panel, minimum | 1.5 mm                                               |

|                                       |            |
|---------------------------------------|------------|
| Thickness of the front panel, maximum | 6 mm       |
| Spacing                               | 65 x 65 mm |

Ambient conditions

|                      |                |
|----------------------|----------------|
| Degree of protection | IP67<br>IP69K  |
| Ambient temperature  | -25 ... +80 °C |

Scope of delivery

|                                           |                                             |
|-------------------------------------------|---------------------------------------------|
| Note (scope of delivery, number and type) | Contact carrier SMF is included in delivery |
|-------------------------------------------|---------------------------------------------|

Pictures

Product picture (catalogue individual photo)



ID: khdrzf03  
| 317.0 kB | .jpg | 352.778 x 483.306 mm - 1000 x 1370 px - 72 dpi  
| 44.7 kB | .png | 73.731 x 101.247 mm - 209 x 287 px - 72 dpi  
| 42.8 kB | .jpg | 89.958 x 123.472 mm - 255 x 350 px - 72 dpi

Schmersal India Pvt. Ltd., Plot No - G-7/1, Ranjangaon MIDC, Tal. - Shirur, Dist.- Pune 412 220  
The details and data referred to have been carefully checked. Images may diverge from original. Further technical data can be found in the manual. Technical amendments and errors possible.  
Generated on: 11/11/2024, 9:19 am