




Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	11/12'24	The first release	PansLee
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!				

综合性能参数Comprehensive performance parameter

- 绝缘电阻Insulation resistance:500MΩ@500VDC
- 介质耐压(初始) Dielectric strength (initial) :同极触点间1800VAC,1Min;
异极触点间1800VAC,1Min;
线圈触点间1800VAC,1Min
Between open contact 1800VAC,1Min;
Between different pole 1800VAC,1Min;
Between contact and coil 1800VAC,1Min

- 负载load:12A
- 螺钉扭力Screw torque:0.8Nm
- 外接导线Wire size:AWG20~14
- 外接导线Wire size:1.5~2.5mm²
- 插拔力Mating&un-mating force:4Kgf Min

安装方式Mounting force

- 标准导轨安装Standard Din-Rail
- 对角螺丝孔安装Flange hole

使用环境Service environment

- 使用环境温度Ambient temperature: -25°~ +50°
- 湿度Ambient humidity: 5%-85%
- 抗冲击Shock resistance: 破坏性 Destruction: 1,000 m/s²
故障 Malfunction: 200 m/s²
- 耐振动Vibration resistance: 破坏性 Destruction: 10 to 55 Hz, 0.5 mm single amplitude (1.0 mm double amplitude)
故障 Malfunction: 10 to 55 Hz, 0.5 mm single amplitude (1.0 mm double amplitude)

- 外壳 Base: 黑色Black PC
- 重量Weight: 大约About68g

插座规格号说明Specification of socket number:
PTF 14 A 00G

改进顺序号 Improvement Version
适用继电器: 14:14 脚 (AL-4C型继电器)
Matched with reply of 14 terminls (Relay Model: AL-4C)
插座型别Socket Type PTF:PTF型

Amphenol ANYTEK				INSPECTION COPY ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD			
TITLE	PTF14A AL4C Industrial relay socket						
PART NO.	PTF14A00G			DWG NO.	8PTF14A-0003		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance	
		PansLee 2024.11.12	PansLee 2024.11.12	SHEET: 01/01		UNIT: mm	0~1 ±0.2
						SCALE: NONE	>1~5 ±0.3
						REV.: B	>5 ±0.4