

# XUMTARAYP015

Photoelectric sensors XUMT, Transparent reflex, Plastic, Sn 2m, IO-Link, Pigtail M12 15cm



## Main

|                               |                                         |
|-------------------------------|-----------------------------------------|
| Range of product              | Telemecanique Photoelectric sensors XU  |
| Series name                   | Application packaging                   |
| Electronic sensor type        | Photo-electric sensor                   |
| Sensor name                   | XUM                                     |
| Sensor design                 | Miniature                               |
| Detection system              | Reflex                                  |
| Material                      | Plastic                                 |
| Type of output signal         | Discrete                                |
| Supply circuit type           | DC                                      |
| Discrete output type          | PNP/NPN autodetect<br>IOLINK            |
| Discrete output function      | 1 NO or 1 NC programmable               |
| Electrical connection         | 1 pre-cabled male connector M12, 4 pins |
| Cable length                  | 0.15 m                                  |
| Product specific application  | Detection of transparent object         |
| Emission                      | Red reflex                              |
| [Sn] nominal sensing distance | 2 m reflex need reflector XUZC50        |

## Complementary

|                            |                                                                  |
|----------------------------|------------------------------------------------------------------|
| Enclosure material         | ABS                                                              |
| Lens material              | PMMA                                                             |
| Maximum sensing distance   | 2 m reflex                                                       |
| Output type                | Solid state                                                      |
| Output function governance | NO/NC programmable                                               |
| Add on output              | Without, 100 mA                                                  |
| Add on input               | Remote teaching                                                  |
| Wire insulation material   | PVC                                                              |
| Status LED                 | 1 LED (green) for power ON<br>1 LED (orange) for output state    |
| [Us] rated supply voltage  | 12...24 V DC with reverse polarity protection                    |
| Supply voltage limits      | 10...30 V DC                                                     |
| Switching capacity in mA   | <= 100 mA (overload and short-circuit protection)                |
| Switching frequency        | <= 1000 Hz                                                       |
| Current consumption        | <= 30 mA no-load                                                 |
| Maximum delay first up     | 300 ms                                                           |
| Maximum delay response     | 500 µs                                                           |
| Maximum delay recovery     | 300 ms                                                           |
| Setting-up                 | Sensitivity adjustment with teach mode<br>Sensitivity by IO-Link |
| Height                     | 34 mm                                                            |
| Length                     | 20 mm                                                            |
| Width                      | 12 mm                                                            |
| Net weight                 | 0.03 kg                                                          |

## Environment

|                                       |                                                                 |
|---------------------------------------|-----------------------------------------------------------------|
| Product certifications                | CE[RETURN]UKCA[RETURN]cULus                                     |
| Ambient air temperature for operation | -25...60 °C                                                     |
| Ambient air temperature for storage   | -20...80 °C                                                     |
| IP degree of protection               | IP67 conforming to IEC 60529<br>IP69K conforming to DIN 40050-9 |

## Packing Units

|                              |          |
|------------------------------|----------|
| Unit Type of Package 1       | PCE      |
| Number of Units in Package 1 | 1        |
| Package 1 Height             | 9.1 cm   |
| Package 1 Width              | 3.1 cm   |
| Package 1 Length             | 6.1 cm   |
| Package 1 Weight             | 34 g     |
| Unit Type of Package 2       | S01      |
| Number of Units in Package 2 | 30       |
| Package 2 Height             | 15 cm    |
| Package 2 Width              | 15 cm    |
| Package 2 Length             | 40 cm    |
| Package 2 Weight             | 1.255 kg |

## Contractual warranty

|          |           |
|----------|-----------|
| Warranty | 18 months |
|----------|-----------|