

## M12 Y-cod 8-pol st/- m/- PUR 5.0m



Image is for illustration purposes only. Please refer to product description.

Part number	21 34 260 0840 050
Specification	M12 Y-cod 8-pol st/- m/- PUR 5.0m
HARTING eCatalogue	<a href="https://b2b.harting.com/21342600840050">https://b2b.harting.com/21342600840050</a>

### Identification

Category	System cabling
Series	Circular connectors M12
Element	Cable assemblies
Specification	Pre-assembled on one side
Connector 1	M12 Y-coding Male Straight
Type of cable	Copper cable (round)

### Version

Cable length	5 m
Number of cores	8
Core structure	4x AWG20 + 1x 4x AWG26
Coding	Y-coding

### Technical characteristics

Limiting temperature	-25 ... +80 °C
----------------------	----------------

### Material properties

Material (cable)	PUR (polyurethane)
Colour (cable)	Green
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes
REACH SVHC substances	Lead
ECHA SCIP number	567c8b78-5fa0-43aa-a4c0-beb9d99b7769
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

Approvals	CE
-----------	----

## Commercial data

Packaging size	1
Net weight	480 g
Country of origin	Germany
European customs tariff number	85444995
GTIN	5713140282599
ETIM	EC001855
eCl@ss	27060311 Assembled sensor actuator-line