

[Calculator](#)[LMR® Cables](#)[Products](#)[Markets & Applications](#)[Resources](#)

## EZ-600-NMC-2-D

N male (plug) straight EZ connector for LMR®-600, TCOM®-600, and T-RAD®-600 type cables. The EZ-600-NMC-2-D eliminates assembly errors and soldering with crimp-style outer contacts and spring finger inner contacts. It features a no-braid trim design, eliminating FOD and guaranteeing an optimal and consistent termination. The BeCu pins are designed to maximize surface contact and minimize current density. They provide a strong spring force making the EZ connectors a perfect choice for extreme cold and high-

### Inventory Status

Distributor	Qty
Mouser Electronics	168
DigiKey	45



Showing 1 to 2 of 2 entries



1



vibration applications where the center conductor might contract. The type N is a durable, weatherproof, medium-size RF connector designed for systems where excellent RF and mechanical performance is critical. They feature a threaded coupling mechanism and are fully interchangeable with N-Type connectors made to the MIL-C-39012 specification.



Stock Code: **3190-2641**

N-male (plug)




**1**




Specs

Compatible with


Documentation



Hardware



CAD Model



Ask an Expert

# Specifications

Part Number	EZ-600-NMC-2-D	Max Frequency (GHz)	6	Pin Finish	Gold
Stock Code	3190-2641	VSWR Freq	<1.35:1	Length (mm)	53
Interface	N	VSWR Frequency (GHz)	6	Length (in)	2.1
				Width (mm)	23.4

<https://timesmicrowave.com/connectors/ez-600-nmc-2-d-coax-connectors/>

3/8

Gender	male (plug)	Coupling Nut	Hex/Knurl	Width (in)	0.92
Orientation	Straight	Inner Contact Attach	Spring Finger	Weight (g)	91.6
PIM Rating	N/A	Outer Contact Attach	Clamp	Weight (lb)	0.2
Impedance (ohms)	50	Body Finish	Alballoy		

Compatible with

LMR-600

LMR-600-DB

LMR-600-FR

LMR-600-FR-PVC

TCOM-600

TCOM-600-FR

T-RAD-600-FR-MSHA

T-RAD-600-PVC

## Tools and Accessories



WR-600



CST-600



Grounding

## Documentation

### EZ-600-NMC-2-D Connector Drawing

[Download](#)

### EZ-600-NMC-2-D Installation Instructions

[Download](#)

### EZ-600-NM

[Dow](#)

## Subscribe to our newsletter!

Interested in receiving email newsletters and other updates from Times? Subscribe now!

First name\*

Last name\*

Company

Email\*

[Subscribe](#)

## Products

[Cables and Assemblies](#)[Connectors](#)[Test and Measurement Products](#)[Tools](#)[Accessories](#)

## Quick Links

[Markets](#)[Applications](#)[Resources](#)[About Us](#)[Careers](#)[News](#)[Privacy Policy](#)

## Markets

[Space](#)[Land, Mobile, Radio and Public Network](#)[Unmanned Aerial Vehicles](#)[Quantum Computing](#)[Test and Measurement](#)

## Contact Us

First name\*

Last name\*

Country \*

Please Select



Email\*

Message



## Follow Us



protected by reCAPTCHA

[Privacy](#) - [Terms](#)

Times Microwave Systems,  
358 Hall Avenue, Wallingford,  
CT 06492, USA  
T: +1 (800) 867-2629  
F: 203-949-8423

Times Microwave Systems,  
Shanghai, China  
T: 86-21-51761234  
F: 021-64424098

Times Microwave Systems,  
No. 65, 2nd Floor, MGM Magnum,  
Electronic City Phase 1, Bengaluru-  
560100  
T: (080) 6861-1611

Copyright © 2024 Times Microwave Systems. All Rights Reserved. InstaBend<sup>®</sup>, LLPL<sup>®</sup>, LLPX<sup>®</sup>, LLSB<sup>®</sup>, LMR<sup>®</sup>, LMR-lite<sup>®</sup>, M8<sup>®</sup>, M8M<sup>®</sup>, MaxGain<sup>®</sup>, Miltech<sup>®</sup>, nu-Trac<sup>®</sup>, PhaseTrack<sup>®</sup>, Smart-Panel<sup>®</sup>, Stripflex<sup>®</sup>, T-COM<sup>®</sup>, Testmate<sup>®</sup>, TF4<sup>®</sup>, T-Flex<sup>®</sup>, Times Microwave Systems<sup>®</sup>, TIMES PROTECT and Design<sup>®</sup>, Times-Protect<sup>®</sup>, T-Rad<sup>®</sup>, TuffGrip<sup>®</sup>, Xtended Flex<sup>®</sup> are Registered Trademarks of Times Microwave Systems.