



Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Not Low Halogen - contains Br or Cl > 900 ppm.
Solder Process Capability	Wave solder capable to 260°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>

Compatible Parts

TE Part # 6-1415035-1
RT78726


TE Part # 1860306-1
RT78725

TE Part # 5-1415036-1
PTML0024

TE Part # 1860200-1
RT7872P




TE Part # 2022103-1
[RT17017](#)



TE Part # 2-1415036-1
[PTMG0024](#)



TE Part # 6-1415036-1
[PTML0524](#)



TE Part # 3-1415036-1
[PTMG0524](#)




TE Part # 1415037-1
[PTMT00LO](#)



TE Part # 9-1415036-1
[PTMT00A0](#)



TE Part # 1415540-8
[RT28816](#)




TE Part # 8-1415036-1
[PTML1024](#)



TE Part # 1860991-1
[RT78602, RELAY SOCKET PCB 5MM](#)

Customers Also Bought



TE Part #5747844-4
[09 MSFL RCPT RA 318 \(IN,FM,BL\)](#)




TE Part #3-644456-6
[06P MTA100 HDR ASSY \(NARROW\)](#)



TE Part #66506-3
[20 DF PIN](#)




TE Part #206434-1
[CPC PLUG ASSEMBLY SIZE 11-8](#)



TE Part #1761606-7
[IDC LOW PRO HDR 20P VERT LG LAT BLK](#)



TE Part #644752-8
[08P MTA156 HDR ASSY SQ STR F/L](#)



TE Part #644752-6
[06P MTA156 HDR ASSY SQ STR F/L](#)



TE Part #5555163-1
[MJ,LPF,R/A,6P/6C,PNL STOPS,BU](#)



Documents

Datasheets & Catalog Pages

Power PCB Relay RT1

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

VDE Certificate

English