



All Small Signal Relay, Axicom P2 Standard (23)

Product Compliance

For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Compliant
EU ELV Directive 2000/53/EC	Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	No Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JUNE 2024 (241) Candidate List Declared Against: JUNE 2024 (241) Does not contain REACH SVHC
Halogen Content	Low Halogen - Br, Cl, F, I < 900 ppm per homogenous material. Also BFR/CFR/PVC Free
Solder Process Capability	Reflow solder capable to 245°C

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulation, the information TE provides on SVHC in articles for this part number is based on the latest European Chemicals Agency (ECHA) 'Guidance on requirements for substances in articles' posted at this URL: <https://echa.europa.eu/guidance-documents/guidance-on-reach>



Compatible Parts

TE Part # 7-1393788-6

V23079G1001B301

TE Part # 6-1393788-2

V23079D1011B301

Also in the Series | Axicom P2 Signal Relay

Electromechanical Relays(44)

Customers Also Bought

TE Part #5188835-1

Z-PACK/B M-HDR 154P.

TE Part #3-644457-3

03P MTA100 HDR ASSY R/A NARROW

TE Part #TAD14141111-005

M12D4-MS-PVC TYPE B-5.0M

TE Part #60445-2

SPADE .137 24-20 AWG TPBR

TE Part #650889-5

096 EURO TYPE R PIN AP ASSY

TE Part #1-2842284-0

10P,2MM,SHRD HDR,DRV,T,0.76AU,TB

TE Part #2-2842238-0

20P,2MM,SHRD HDR,DRV,T,0.76AU,TB

TE Part #YDTS20W25-35SNV001

RECP ASSY



Documents

Product Drawings

V23079D1001B301

English

CAD Files

3D PDF

3D

Customer View Model

ENG_CVM_CVM_5-1393788-5_F1.2d_dxf.zip

English

Customer View Model

ENG_CVM_CVM_5-1393788-5_F1.3d_igs.zip

English

Customer View Model

ENG_CVM_CVM_5-1393788-5_F1.3d_stp.zip

English

By downloading the CAD file I accept and agree to the [Terms and Conditions](#) of use.

Datasheets & Catalog Pages

Axicom Signal and High Frequency Relays (RF Switches) APPLICATION NOTE #2

English

Transportation, Storage, Handling, Assembly and Testing of AXICOM SMT Relays

English

P2 Relay Datasheet

English

Product Specifications

Definitions General Purpose Relays

English

Agency Approvals

UL

English