

Part number

APV 11



Painted distribution box, AP series, external dimensions 115x140x61 mm / internal dimensions 103x128x46 mm

Product description		Material properties	
Product type	Painted distribution box	Main material	Aluminium die-cast
Series	AP	Other materials	Gasket: Polyurethane (PUR) Screws: galvanized steel
Size	External dimensions 115x140x61 mm / internal dimensions 103x128x46 mm	Colour	RAL 7040 grey
Technical data		RoHs conformity	Compliant with exemption 6(c): copper alloy containing up to 4% lead by weight
IP degree of protection	IP66 / IP67	China RoHs - EFUP	50
Further technical details		REACH SVHC substances	Yes Lead
Weight	412,50 g	SCIP number	A4d990c2-7936-4d11-a722-eb8d5d39ca82
Operating temperature range (min, max)	-40°C...+110°C	General ordering information	
		EAN13 code	8015747001779
Packaging Information			
Packaging length	570,00 mm	Packaging height	250,00 mm
Packaging width	350,00 mm	Packaging weight	17,70 kg
Packaging volume	49,88 dm ³	Packaging description	Carton box
Packaging quantity	40 Pcs	Packaging EAN code	8015747261807
Sub-packaging weight	0,44 kg	Sub-packaging description	Plastic packaging
Sub-packaging quantity	1 Pcs	Sub-packaging EAN barcode	8015747200028

Part number

APV 11



Notes

- Earth terminal kit for the cover (APR T)
 - Optional stainless steel screws (AP M5X)
-

California Proposition 65 Information



WARNING

This product can expose you to lead and its compounds, known to the State of California to cause cancer and/or reproductive toxicity. For more information go to www.P65Warnings.ca.gov.

Dimensions shown in mm are not binding and may be changed without notice.
