

Eaton C25FNF350A

Catalog Number: C25FNF350A

Eaton definite purpose contactor, Quick, 50A, 110-120 Vac, 50/60 Hz, Open with metal mounting plate, 15-50A, Contactor, Three-pole, 65A, Box lugs (posidrive setscrew) and quick connect terminals (side-by-side), Non-reversing

General specifications



Product Name

Eaton definite purpose contactor

Catalog Number

C25FNF350A

UPC

782113476070

Product Length/Depth

3.97 in

Product Height

3.75 in

Product Width

2.63 in

Product Weight

2.7 lb

Warranty

1 year

Compliances

RoHS Compliant

Certifications

UL Recognized
CSA Certified

Catalog Notes

Resistive Load rating per pole

Product specifications

Amperage Rating

50A

Number Of Poles

Three-pole

Type

Non-reversing

Coil

110-120 Vac, 50/60 Hz

Enclosure

Open with metal mounting plate

Frame size

15-50 A, two-pole and three-pole

Inductive full load

50 A

Model

Contactor

Resistive load

65 A

Terminals

Box lugs (posidrive setscrew) and quick connect terminals (side-by-side)

Connection

Quick

Resources

Specifications and datasheets

[Eaton Specification Sheet - C25FNF350A](#)