



xlrCON TOP series

Portfolio & Comparison

Portfolio	xlrCON TOP	xlrCON TOP airtight
	 NC3FDX-TOP	 NC3FDXX-TOP
	 NC3MDX-TOP	 NC3MDXX-TOP
	 NC4FDX-TOP	N/A
	 NC4MDX-TOP	N/A



xlrCON TOP series

Portfolio & Comparison

	 NC5FDX-TOP	 NC5FDXX-TOP
	 NC5MDX-TOP	 NC5MDXX-TOP
	 NC10FDX-TOP	N/A
	 NC10MDX-TOP	N/A
Rated IP	IP65	IP65 + IP66 + Airtightness
Fire enclosure	UL94 V-0	According to IEC 62368-1, EN IEC 62368-1, UL 62368-1, C22.2 No. 62368-1
Outdoor enclosure	-	According to IEC 62368-1, EN IEC 62368-1, UL 62368-1, C22.2 No. 62368-1
UV protection	Yes	Yes
Corrosion resistance	Yes	Yes
Color	Black + Silver (Push)	Black
Mechanical properties	-	D-Size & D-Shape
ESD protection	-	Yes (up to 2kV)